

# ZS10-BR



Products Low Voltage Products and Systems Connection Devices Terminal Blocks SNK Series

## General Information

<b>Extended Product Type:</b>	ZS10-BR
<b>Product ID:</b>	1SNK508064R0000
<b>EAN:</b>	3472595080649
<b>Catalog Description:</b>	ZS10-BR Screw Clamp Terminal Block - Feed-through - Brown
<b>Long Description:</b>	- Save space by connecting conductors up to 10 mm <sup>2</sup> (without insulated ferrule, CB certified) 6 AWG in just 8 mm 0.315 in spacing, - Perfectly adapted to solar applications: voltage is rated 1000 V AC / DC IEC.

## Additional Information

<b>ABB Industrial IT Suite:</b>	Control IT
<b>ATEX Certificate:</b>	1SND162004A1707
<b>Ambient Air Temperature:</b>	Operation -55 ... +110 °C Storage -55 ... +110 °C
<b>Ambient Temperature:</b>	-5 ... +40 °C
<b>BV Certificate:</b>	1SND161073A0204
<b>CB Certificate:</b>	1SND161018A0202
<b>CSA Certificate:</b>	1SND161070A0209
<b>Color:</b>	Brown
<b>Connecting Capacity Main Circuit UL/CSA:</b>	Screw Clamp / Flexible 1x 24 ... 6 AWG Screw Clamp / Flexible 2x 20 ... 12 AWG Screw Clamp / Rigid 1x 24 ... 6 AWG Screw Clamp / Rigid 2x 20 ... 12 AWG Screw Clamp / With Insulated Ferrule 1x 24 ... 10 AWG Screw Clamp / Without Insulated Ferrule 1x 24 ... 8 AWG Screw Clamp / With Twin Ferrule 2x 20 ... 12 AWG
<b>Connecting Capacity UL/CSA:</b>	Stranded 6 AWG
<b>Connecting Capacity Main Circuit:</b>	Screw Clamp / Flexible 1x 0.5 ... 10 mm <sup>2</sup> Screw Clamp / Flexible 2x 0.5 ... 4 mm <sup>2</sup> Screw Clamp / Rigid 1x 0.5 ... 10 mm <sup>2</sup> Screw Clamp / Rigid 2x 0.5 ... 4 mm <sup>2</sup> Screw Clamp / With Insulated Ferrule 1x 0.5 ... 6 mm <sup>2</sup> Screw Clamp / Without Insulated Ferrule 1x 0.5 ... 10 mm <sup>2</sup> Screw Clamp / With Twin Ferrule 2x 0.5 ... 4 mm <sup>2</sup>
<b>Connection Type:</b>	Screw clamp
<b>Country of Origin:</b>	France (FR)
<b>Customs Tariff Number:</b>	85369010
<b>DNV Certificate:</b>	1SND161087A0202
<b>Data Sheet, Technical Information:</b>	1SNK161004D0201
<b>Declaration of Conformity - CE:</b>	1SND225112U1001
<b>Degree of Protection:</b>	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
<b>Dielectric Test Voltage:</b>	2200 V
<b>E-nummer:</b>	2925963
<b>EAC Certificate:</b>	1SND161010A1100
<b>EAN:</b>	3472595080649
<b>ETIM 4:</b>	EC000897 - Feed-through terminal block
<b>ETIM 5:</b>	EC000897 - Feed-through terminal block
<b>ETIM 6:</b>	EC000897 - Feed-through terminal block
<b>Environmental Information:</b>	1SND220071E1000
<b>Flammability According to UL94:</b>	V0

Function:	Feed-through
Gauge Type:	A5-B5
IIT Publishing Status:	Level 0 - Information enabled
Industrial IT Certification Level:	0
Instructions and Manuals:	1SNK160027C0201
Insulation Material:	Polyamide
Invoice Description:	ZS10-BR Screw Clamp Terminal Block - Feed-through - Brown
Maximum Operating Voltage UL/CSA:	Main Circuit 600 V
Minimum Order Quantity:	50 piece
Mounting on DIN Rail:	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Number of Connections:	2
Number of Levels:	1
Object Classification Code:	X
Order Multiple:	50 piece
Package Level 1 EAN:	3472595080649
Package Level 1 Gross Weight:	0.705 kg
Package Level 1 Height:	52 mm
Package Level 1 Length:	252 mm
Package Level 1 Units:	50 piece
Package Level 1 Width:	82 mm
Package Level 2 Gross Weight:	9.020 kg
Package Level 2 Height:	200 mm
Package Level 2 Length:	400 mm
Package Level 2 Units:	600 piece
Package Level 2 Width:	300 mm
Package Level 3 Units:	28800 piece
Pollution Degree:	3
Power Loss:	1.8 W
Product Main Type:	ZS10
Product Name:	Terminal Block
Product Net Depth:	47.3 mm
Product Net Height:	53 mm
Product Net Length:	47.3 mm
Product Net Weight:	14.1 g
Product Net Width:	8 mm
Product Packing Type:	Box
RINA Certificate:	1SND161088A0200
RMRS Certificate:	1SND161008A1101
Rated Cross-Section:	10 mm <sup>2</sup>
Rated Current (I <sub>n</sub> ):	Main Circuit 57 A
Rated Impulse Withstand Voltage (U <sub>imp</sub> ):	8000 V
Rated Short-time Withstand Current (I <sub>cw</sub> ):	for 1 s 1200 A
Rated Voltage (U <sub>r</sub> ):	1000 V
Recommended Screw Driver:	4 mm
Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant
RoHS Date:	20050818
RoHS Information:	1SND230491F0206

1622005A1706

1622005A1706

<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment
<b>Selling Unit of Measure:</b>	piece
<b>Short Description:</b>	ZS10-BR Screw Clamp Terminal Blocks
<b>Short-Circuit Current Rating (SCCR):</b>	100 kA
<b>Spacing:</b>	8 mm
<b>Sub-Function:</b>	2 connections
<b>Sub-Function 3:</b>	2 connections
<b>Wire Stripping Length:</b>	12.0 mm
<b>cUL Certificate:</b>	1SND161040A0206
<b>Number of Potentials:</b>	1
<b>IECEX Certificate:</b>	1SND162005A1706

