



LOC	DIST	REVISIONS					
AJ	16	P	LTR	DESCRIPTION	DATE	DWN	APVD
		A1		REVISED PER ECO-11-005030	11MAR11	RK	HMR



RECOMMENDED PANEL CUTOUT



RECOMMENDED STRIP LENGTH

- 1 MAX PANEL THICKNESS .240.
- 2 USE WITH PRO-CRIMPER 354940-1.
3. USE INSTRUCTION SHEET 408-9763.
- 4 BULK KIT PACKAGE, 100 PER BAG.

4	CUSTOM CABLE		—	—	222001-6	227194-2	329633	1-329631-2	1-329632-2	9-413658-2	1-413746-0	413744-2	2-5413590-1
	AT&T 735A	4.52 [.178]	1.07 [.042]	58425-2	—	—	329633	1-329631-2	1-329632-2	9-413658-2	1-413746-0	413744-2	1-5413590-8
	CUSTOM CABLE, C/C-24AWG, DOD-.109, JOD-.153	4.52 [.178]	1.07 [.042]	58425-2	—	—	329633	1-329631-2	1-329632-2	9-221132-6	413746-5	413744-2	1-5413590-7
	RG-179/U & 187/U	4.52 [.178]	1.07 [.042]	58425-2	222001-6	227194-2	329633	1-329631-2	1-329632-2	9-413658-0	1-413746-5	413744-2	5413590-8
	AT&T KS 19224 L2 AND JIS 1.5C-XV	4.52 [.178]	1.07 [.042]	58425-2	222001-6	227194-2	329633	1-329631-2	1-329632-2	9-413658-2	1-413746-5	413744-2	5413590-4
	BELDEN 8218 AND JIS 2.5C-2V	4.52 [.178]	1.07 [.042]	58425-2	—	—	329633	1-329631-2	1-329632-2	9-221132-6	1-413746-0	413744-2	5413590-3
FOR USE WITH CABLE		FERRULE (HEX)	CONTACT (SQ)	DIE SET	⑧ TUBING, METAL QTY=1	⑦ TUBING, PLASTIC QTY=1	⑥ GASKET QTY=1	⑤ JAM NUT QTY=1	④ LOCKWASHER QTY=1	③ FERRULE QTY=1	② CONTACT QTY=1	① JACK ASSY QTY=1	PART NUMBER
		CRIMP HEIGHTS											

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

0 PLC ± -

1 PLC ± -

2 PLC ± 0.41 [.016]

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH -

DWN L. VARELA - 22APR2005

CHK J. HAVENER - 22APR2005

APVD J. LIPPERT - 22APR2005

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

JACK, BULKHEAD, 75 OHM, HEX CRIMP, BNC

SIZE A1 CAGE CODE 00779 DRAWING NO 5413590

RESTRICTED TO -

SCALE 5:1 SHEET 1 OF 1 REV A1