

LabelWriter™ 4XL



Heavy-Duty High-Speed Label Printer

- Prints labels up to 104 mm wide, including 104 x 159 mm shipping labels, warehouse labels, barcode and identification labels, bulk mailing labels and other large-format labels
- Prints all DYMO LW labels – 60+ sizes and styles in all
- Print speeds up to 129 labels per minute* or 81.28 mm per second (ips)
- 300 dpi resolution for precise barcodes and clear, legible text and graphics
- Uses thermal printing technology – never needs ink or toner



* High-capacity label



Single Unit Includes:

- LabelWriter 4XL Label Printer
- 104 x 159 mm Extra Large Shipping Labels
- Adapter
- Power Cable
- USB Cable
- Quick Start Guide
- Cleaning Card
- DYMO® Label™ v.8 Software Installation CD

Quick Specs	
Unit Dimensions (L x W x H)	178 x 187 x 134mm
Weight	1.7kg
Mac®/PC Compatible	Yes
Max Label Width	104mm
Resolution	600 x 300 dpi
Printing System	Direct Thermal
Print Speed	129 labels/minute*
Barcodes	Yes
Power Source	AC Adapter
Networking	Print Server Sold Separately
Country of Origin	China

* High-capacity label

Item Number	Description		Length (cm)	Width (cm)	Height (cm)	Weight (kg)	QTY	EAN	Customer Price
S0904960	LabelWriter 4XL ENG-UK/HK	Unit	25.5	26.0	24.0	1.7	1	3501170838969	
		Shelf	-	-	-	-	-	-	
		Case	51.0	28.0	27.0	-	3	13501170838966	
		Pallet	120.0	80.0	120.2	-	60	-	



Accessories									
Item Number	Description	Unit	Length (cm)	Width (cm)	Height (cm)	Weight (kg)	QTY	EAN	Customer Price
931160	Switching Adapter	Unit	29.7	24.2	16.3	0.5	1	-	
1762422	Spool 4XL	Unit	9.2	9.2	13.1	0.10	1	-	

Print one label or hundreds – without the waste and hassles of sheet labels.

Label Type	Description	Code #	Size in mm	Labels/Roll	Rolls/Box	Adhesive	Material
Mailing	Standard Address Labels	S0722370	28 x 89	130	2	Permanent	Paper
	Standard Address Labels	S0722360	28 x 89	130	24	Permanent	Paper
	High Capacity Address Labels	S0947410	89 x 28	1050	2	Permanent	Paper
	Assorted Colour labels	S0722380	28 x 89	130	2	Permanent	Paper
	Large Address Labels	S0722400	36 x 89	260	2	Permanent	Paper
	Large Address Labels	S0722390	36 x 89	260	24	Permanent	Paper
	Large Address Labels	S0722410	36 x 89	260	1	Permanent	Transparent Plastic
	Large Return Address Label	S0722520	25 x 54	500	1	Permanent	Paper
Shipping	Shipping / Name badge Labels	S0722430	54 x 101	220	1	Permanent	Paper
	High Capacity Shipping Labels	S0947420	102 x 59	575	2	Permanent	Paper
	Shipping / Name badge Labels	S0722420	54 x 101	220	12	Permanent	Paper
	Extra Large Shipping Labels	S0904980	104 x 159	220	1	Permanent	Paper
Multi-Purpose	Multi-Purpose Labels	S0722530	13 x 25	1000	1	Removable	Paper
	Square Multi-Purpose Labels	S0929120	25 x 25	750	1	Removable	Paper
	Multi-Purpose Labels	S0722550	19 x 51	500	1	Removable	Paper
	Multi-Purpose Labels	S0722540	57 x 32	1000	1	Removable	Paper
	Large Multi-Purpose Labels	S0722440	54 x 70	320	1	Permanent	Paper
Specialty	Suspension file labels	S0722460	12 x 50	220	1	Permanent	Paper
	LAF Labels small	S0722470	38 x 190	110	1	Permanent	Paper
	LAF Labels large	S0722480	59 x 190	110	1	Permanent	Paper
	Small name badge label	S0722560	41 x 89	300	1	Removable	Paper
	Appointment / name badge cards	S0929100	51 x 89	300	1	Non-adhesive	Paper
	Large name badge cards	S0929110	62 x 106	250	1	Non-adhesive	Paper
	CD Labels	S0719250	57 diameter	160	1	Permanent	Paper

Country of Origin: Belgium



DISTRIBUTED BY:
 Newell Europe Sàrl
 Chemin de Blandonnet 10
 1214 Vernier – Switzerland
 WWW.DYMO.COM



A *NewellRubbermaid* Brand

This information is being provided for general information purposes and the compliance standards and certifications referenced herein are based on current standards which are subject to change.

©2014 Newell Europe LLC

A Newell Rubbermaid Company™	 <small>NRM Mirra Business Park Chennai - 2, 201-1801 No. 143, Dr.M.G. Road Santhoshnagar Chennai 600 096 India T: 91 44 4253 7777 www.schawk.com</small>	 CYAN MAGENTA YELLOW BLACK		
	Use the PANTONE MATCHING SYSTEM for accurate color reproduction			
	VERSION	JOB DESCRIPTION : NRM_EU_Writing_Dymo_1362812_EMEA Product Handbooks_UK Masters FILE NAME : DY_1362812_2014_EMEA_LW4XL_TechSheet_v7.indd	BRAND : WRITING-DYMO	
	7 <small>DATE : 10-01-2014 OPERATOR : MKS</small>	<small>SCHAWK JOB # : 310253B NRM JOB # : 1362812 COMPONENT # : N/A</small>	<small>CATEGORY OF WORK : COLLATERALS-FACT BOOKS NO. OF PAGES# : 2 PAGES SIZE : A4</small>	
NOTE :				