

ROLINE Gigabit Ethernet Switch, 8 Ports

Supplier: Roline
Item No.: 21.14.3517

roline
Designed for Professionals



Description

The ROLINE Gigabit Ethernet Switches are ideal as network centres for small to medium sized fast LANs. The gigabit ethernet ports can be connected to a server and sub-networks (with one of the ROLINE 10/100 switches with gigabit uplink).

- 8x 10/100/1000Mbit/s ports
 - Provide Store-and-Forward architecture, full wire speed filtering and forwarding rates
 - Support Auto-MDI/MDI-X on all ports
 - Support full/half duplex modes and auto-negotiation on all ports
 - Support flow control: back pressure for half-duplex mode, IEEE 802.3x for full-duplex mode
 - Automatic source address learning and aging
 - Stores up to 8K MAC-addresses
 - Supports Jumbo Frame in all three speeds (10/100/1000Mbit/s)
 - Front-panel diagnostic LEDs
-
- **Contents:** Switch, power supply, manual

Technical Data

Dimensions (HxWxD)	31x183x125 mm
Auto-Negotiation	Yes

Full duplex	Yes
Casing	Desktop
Gigabit Ethernet Ports RJ-45	8
LAN (Mbps)	10/100/1000
Power consumption	9VDC 700mA
Fan	No
MAC addresses	8K
Managed	No
Power supply unit (internal/external)	External
Network standard	Gigabit Ethernet
Port Trunking	No
Product group	Network switches
Conveyance good	No
Stackable	No
Switch Layer	2
Switch Type	Store-and Forward
Switching Fabric Type	Non blocking
VLAN	No

Shipment

Switch
power supply
manual

We reserve the right to amend typing errors/mistakes to price lists and technical data at any time. Pictures can be different from the original.

Questions

If you have any questions about this item, contact us:
Phone: 01293 565556
E-Mail: sales@rotronic.co.uk