


C4C, Film, Metallized Polypropylene, Power, 0.01 uF, 5%, 750 VAC, 3000 VDC, 70°C

**Dimensions**

D	12mm NOM
L	33mm NOM
LL	40mm +/-5mm
F	0.8mm NOM

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	300

General Information

Supplier:	KEMET
Series:	C4C
Dielectric:	Metallized Polypropylene
Style:	Axial
RoHS:	Yes
Lead:	Wire Leads
Miscellaneous:	Polyester Tape & Resin Protection

Specifications

Capacitance:	0.01 uF
Capacitance Tolerance:	5%
Voltage AC:	750 VAC
Voltage DC:	3000 VDC
Temperature Range:	-40/+85C
Rated Temperature:	70°C
Dissipation Factor:	0.05%
Max dV/dt:	2100 V/us
Resistance:	90.3 mOhms (100kHz)
Ripple Current:	3 Amps (100kHz 70C), 21 Amps (Peak)