




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
AD	00		M	EC 0G3C 0734 04	18DEC04	BSV
			M1	REVISED PER ECO-09-020689	02SEP09	KK

13	OBSOLETE	12	2	2.40	1.198	1-104257-1	12	6-103959-1
13	OBSOLETE	12	2	2.20	1.098	1-104257-0	1 1	6-103959-0
		12	2	2.00	.998	104257-9	10	5-103959-9
		12	2	1.80	.898	104257-8	9	5-103959-8
		12	2	1.60	.798	104257-7	8	5-103959-7
13	OBSOLETE	12	2	1.40	.698	104257-6	7	5-103959-6
		12	4	2.39	.598	104257-5	6	5-103959-5
		12	4	1.99	.498	104257-4	5	5-103959-4
		12	5	1.99	.398	104257-3	4	5-103959-3
		12	8	2.40	.298	104257-2	3	5-103959-2
		12	10	2.00	.198	104257-1	2	5-103959-1
		10	5	1.99	.398	104257-3	4	1-103959-3
	11	10	4	1.99	.498	104257-4	5	1-103959-2
13	OBSOLETE	9	2	2.40	1.198	1-104257-1	12	1-103959-1
13	OBSOLETE	9	2	2.20	1.098	1-104257-0	1 1	1-103959-0
		9	2	2.00	.998	104257-9	10	103959-9
13	SUPERSEDED	9	2	1.80	.898	104257-8	9	103959-8
		9	2	1.60	.798	104257-7	8	103959-7
13	OBSOLETE	9	2	1.40	.698	104257-6	7	103959-6
		9	4	2.39	.598	104257-5	6	103959-5
		9	4	1.99	.498	104257-4	5	103959-4
		9	5	1.99	.398	104257-3	4	103959-3
		9	8	2.40	.298	104257-2	3	103959-2
		9	10	2.00	.198	104257-1	2	103959-1
PLATING		6	B	A	HOUSING PART NUMBER	NO OF POSN	ASSEMBLY PART NUMBER ON STRIP	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± .02
3 PLC ± .005
4 PLC ± -
ANGLES ± -
FINISH SEE TABLE

MATERIAL

HOUSING:

DWN L A MAYER 11-4-86
CHK P de Jong 11-12-86
APVD P de Jong 11-12-86

PRODUCT SPEC 108-25034
APPLICATION SPEC 114-25026

WEIGHT -

CUSTOMER DRAWING

Tyco Electronics Tyco Electronics Corporation Harrisburg, Pa 17105-3608

NAME RCPT ASSY, AMPMODU MTE, SINGLE ROW .100 C/L, LATCHED AND POLARIZED FOR #26-#30 AWG WIRE SIZE, STRIP FORM

SIZE A2 CAGE CODE 00779 DRAWING NO C=103959

RESTRICTED TO -

SCALE 4:1 SHEET 1 OF 1 REV M1