




NOTE
1. GENERAL TOLERANCE: ± 0.5 , $\pm 3^\circ$
2. WARPAGE PERMITTED MAX. 6mm
3. APPLICATION TEST SPEC:
MS210-06-A2[EXT-2](EXCEPT 4.4)

BLACK	PA66-GF30	LEVER HSG	1897645-2
COLOR	MATERIAL	DESCRIPTION	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC $\pm$

1 PLC $\pm$

2 PLC $\pm$

3 PLC $\pm$

4 PLC $\pm$

ANGLES $\pm$

FINISH -

DWN

YH MA

CHK

YM CHOI

APVD

HG CHO

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

Tyco Electronics
Kyungsan, Korea

NAME

LEVER HSG FOR 60P

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=1897645

SCALE

SHEET

OF

REV

A