

Specifications for BMP71 Label Printer Labels

Adhesive	Permanent Acrylic
Article No.	115093
Brady Material No.	B-427
Material Type	Self-laminating Vinyl
Colour	White/Transparent
Finish	Matt
Order Reference	M71-32-427
Printable Area - Height (mm)	12.70
Printable Area - Width (mm)	38.10
Printer Compatibility	BMP71
Size - Height (mm)	38.10
Size - Width (mm)	38.10
Additional Information	Self-Laminating;Self-Extinguishing;Excellent water & oil resistance;Excellent abrasion and smudge resistance
Thickness (mm)	0.102
Total Qty per Pack	250 Label(s) / Box
Vertical Repeat (mm)	41.28
Wire Gauge	7 to 0
Approval/Compliance	UL Recognised
Ribbon Series	M71-R4300
Application	Voice & Data Communication; Wire & Cable Marking
Industry	Aerospace;Data & Telecommunications;Defence;Electrical;Mass Transit
Description	Labels for the BMP™71 Label Printer. Please Note: This material is UL Approved with its respective ribbon. See the Recommended Ribbon Series for the appropriate ribbon to use.
Max. Characters per Line	37
Max. Lines of	5

Text	
Max. Service Temp. °C	60
Max. Wire/Cable Diameter (mm)	8.10
Min. Service Temp. °C	-80
Min. Wire/Cable Diameter (mm)	4.00
Shape	Square
Surface	For smooth & textured/rough surfaces
Voice/Data Application	CAT 5; 4 Pair UTP