

LabelWriter™ 450 Duo



Paper and Plastic Label and Postage Printer for PC and Mac®

- Add versatility to your label printing — print both DYMO LW paper labels and DYMO D1 plastic labels in a variety of sizes and colors
- Label, mail, and file smarter with DYMO® v.8 Label™ software
- Customize and print address, shipping, file folder and barcode labels, plus name badges—all from your PC or Mac®*
- Save time – create labels directly from text in Microsoft® Word, Excel®, Outlook®, QuickBooks® and other programs
- Easily create address and shipping labels — built-in address book prints labels from Outlook® Contacts or Mac® Address Book
- Create custom labels from 60+ label styles and layouts

* Compatible with Windows Vista®, Windows® 7, Windows® 8, Mac OS® X 10.5 or later – Intel® only



Single Unit Includes:

- LabelWriter 450 Duo Label Printer
- Address Labels Starter Roll
- D1 24mm x 3m Black On White Starter Label Cassette
- Adapter
- Power Cable
- USB Cable
- Quick Start Guide
- Cleaning Card
- DYMO® Label™ Software Installation CD



Quick Specs

Unit Dimensions L x W x H)	140 x 197 x 183mm
Weight	2.4 Kg
Mac®/PC Compatible	Yes
Max Label Width	62mm LW and 24mm D1
Resolution	600 x 300 dpi on LW 180 dpi on D1 Labels
Printing System	LW: Direct Thermal D1: Thermal Transfer
Print Speed	71 labels/minute
Barcodes	Yes
Power Source	AC Adapter
Networking	Print Server Sold Separately
Country of Origin	China

* 4-line address label

Item Number	Description		Length (cm)	Width (cm)	Height (cm)	Weight (Kg)	QTY	EAN	Customer Price
S0838960	LabelWriter 450 Duo ENG-UK/HK	Unit	14.9	29.9	22.5	2.8	1	3501170838969	
		Shelf	-	-	-	-	-	-	
		Case	46.0	30.8	24.7	-	3	13501170838966	
		Pallet	120.0	80.0	113.8	-	60	-	
925106	USB Cable	Unit	-	-	-	-	-	-	
923772	Power Cable	Unit	-	-	-	-	-	-	
922983	Cleaning Card	Unit	-	-	-	-	-	-	
931160	Switching Adapter	Unit	29.7	24.2	16.3	0.5	1	-	
S0787940	Spool 450 series	Unit	-	-	-	-	-	-	

LabelWriter™ 450 Duo | Compatible Labels



D1 Standard

For hundreds of tasks around the office or home office, such as filing, storage and asset management.

Temperature rating: -18°C to 90°C

D1 Compatible Labels													
Width	Length	A	A	A	A	A	A	A	A	A	A	A	A
D1 STANDARD													
6mm	7m	S0720780	S0720770	S0720790	–	–	–	–	–	–	–	–	–
9mm	7m	S0720680	S0720670	S0720730	S0720710	S0720740	S0720720	–	–	S0720690	–	S0720700	–
12mm	7m	S0720530	S0720500	S0720580	S0720560	S0720590	S0720570	S0720600	S0720610	S0720540	S0720510	S0720550	S0720520
19mm	7m	S0720830	S0720820	S0720880	S0720860	S0720890	S0720870	S0720900	S0720910	S0720840	–	S0720850	–
24mm	7m	S0720930	S0720920	S0720980	S0720960	S0720990	S0720970	S0721000	S0721010	S0720940	–	S0720950	–



IND Vinyl**

Ideal for both indoor and outdoor applications. Available in the widest range of colors that meet OSHA, ANSI and ISO color standards.

Cold/Heat Resistance: -40°C to 80°C
Length: 5.5 m

- UL recognized as a component to UL 969
- RoHS compliant

IND Permanent Polyester

Professional, polished finish ideal for panels, blocks, faceplates, shelves, bins, beams and more.

Cold/Heat Resistance: -40°C to 150°C
Length: 5.5 m

- UL recognized as a component to UL 969
- RoHS compliant

IND Flexible Nylon

Specifically designed for curved surfaces and wire and cable marking.

Cold/Heat Resistance: -10°C to 80°C
Length: 3.5 m

- UL recognized as a component to UL 969
- RoHS compliant

IND Heat-Shrink Tube

For high-end cable identification. A 3:1 shrink ratio helps ensure a secure fit on wires and cables.

Cold/Heat Resistance: -55°C to 135°C
Length: 1.5 m

- UL recognized as a component to UL 224
- Meets MIL-STD-202G, MIL-M-81531 and SAE-OTL 23053/5 (Class 1 & 3)
- RoHS compliant

For use with LabelManager® series and LabelWriter® 450 Duo and Rhino™ series
*Only compatible with Rhino™ labeling tools

IND Compatible Labels													
Width	Length	A	A	A	A	A	A	A	A	A	A	A	A
IND VINYL													
9mm	5.5 m	18443	–	–	–	–	–	1805437	–	–	–	–	–
12mm	5.5 m	18444	–	18432	18435	1805413	1805416	1805435	1805414	1805243	1805415	1805412	–
19mm	5.5 m	18445	–	18433	18436	1805419	1805422	1805436	1805420	1805417	1805421	1805418	–
24mm	5.5 m	1805430	–	1805431	1805427	1805425	1805429	1805432	1805426	1805423	1805428	1805424	–
IND PERMANENT POLYESTER													
6mm	5.5 m	1805442	1805440	–	–	1805441	–	–	–	–	–	–	–
9mm	5.5 m	18482	18508DMO	–	–	18485	–	–	–	–	–	–	–
12mm	5.5 m	18483	622289	–	–	18486	–	–	–	–	–	–	–
19mm	5.5 m	18484	622290	–	–	18487	–	–	–	–	–	–	–
24mm	5.5 m	1734523	1805433	–	–	1805434	–	–	–	–	–	–	–
IND FLEXIBLE NYLON													
12mm	3.5 m	18488	–	18490	–	–	–	–	–	–	–	–	–
19mm	3.5 m	18489	–	18491	–	–	–	–	–	–	–	–	–
24mm	3.5 m	1734524	–	1734525	–	–	–	–	–	–	–	–	–
IND HEAT-SHRINK TUBE													
6mm	1.5 m	18051	–	18052	–	–	–	–	–	–	–	–	–
9mm	1.5 m	18053	–	18054	–	–	–	–	–	–	–	–	–
12mm	1.5 m	18055	–	18056	–	–	–	–	–	–	–	–	–
19mm	1.5 m	18057	–	18058	–	–	–	–	–	–	–	–	–
24mm	1.5 m	1805443	–	1805444	–	–	–	–	–	–	–	–	–

Country of Origin: Belgium

LabelWriter™ 450 Duo | Compatible Labels



Print one label or hundreds – without the waste and hassles of sheet labels.

Label Type	Description	Code #	Size in mm	Labels/Roll	Rolls/Box	Adhesive	Material
Mailing	Standard Address Labels	S0722370	28 x 89	130	2	Permanent	Paper
	Standard Address Labels	S0722360	28 x 89	130	24	Permanent	Paper
	High Capacity Address Labels*	S0947410	89 x 28	1050	2	Permanent	Paper
	Assorted Colour labels	S0722380	28 x 89	130	2	Permanent	Paper
	Large Address Labels	S0722400	36 x 89	260	2	Permanent	Paper
	Large Address Labels	S0722390	36 x 89	260	24	Permanent	Paper
	Large Address Labels	S0722410	36 x 89	260	1	Permanent	Transparent Plastic
	Large Return Address Label	S0722520	25 x 54	500	1	Permanent	Paper
Shipping	Shipping / Name badge Labels	S0722430	54 x 101	220	1	Permanent	Paper
	High Capacity Shipping Labels*	S0947420	102 x 59	575	2	Permanent	Paper
	Shipping / Name badge Labels	S0722420	54 x 101	220	12	Permanent	Paper
	Extra Large Shipping Labels*	S0904980	104 x 159	220	1	Permanent	Paper
Multit-Purpose	Multi-Purpose Labels	S0722530	13 x 25	1000	1	Removable	Paper
	Square Multi-Purpose Labels	S0929120	25 x 25	750	1	Removable	Paper
	Multi-Purpose Labels	S0722550	19 x 51	500	1	Removable	Paper
	Multi-Purpose Labels	S0722540	57 x 32	1000	1	Removable	Paper
	Large Multi-Purpose Labels	S0722440	54 x 70	320	1	Permanent	Paper
Specialty	Suspension file labels	S0722460	12 x 50	220	1	Permanent	Paper
	LAF Labels small	S0722470	38 x 190	110	1	Permanent	Paper
	LAF Labels large	S0722480	59 x 190	110	1	Permanent	Paper
	Small name badge label	S0722560	41 x 89	300	1	Removable	Paper
	Appointment / name badge cards	S0929100	51 x 89	300	1	Non-adhesive	Paper
	Large name badge cards	S0929110	62 x 106	250	1	Non-adhesive	Paper
	CD Labels	S0719250	57 diameter	160	1	Permanent	Paper

* Label specific to LabelWriter™ 4XL

Country of Origin: Belgium

DISTRIBUTED BY:
Newell Europe Sàrl
Chemin de Blandonnet 10
1214 Vernier – Switzerland
WWW.DYMO.COM



A **Newell Rubbermaid** Brand

This information is being provided for general information purposes and the compliance standards and certifications referenced herein are based on current standards which are subject to change.

©2014 Newell Europe LLC

A NewellRubbermaid Company™	SCHAWK! RMC MBBWA Business Park Campus +2, 5th Floor No. 143, D-AM, G. R. Road Kandanchavadi, Chennai 600 086 India T +91 44 4533 7777 www.schawk.com	CYAN MAGENTA YELLOW BLACK	Use the PANTONE MATCHING SYSTEM for accurate color reproduction	
	VERSION	JOB DESCRIPTION : NRM_EU_Writing_Dymo_1362812_EMEA Product Handbooks_UK Masters	BRAND : WRITING-DYMO	
	7 DATE : 10-10-2014 OPERATOR : GV	FILE NAME : DY_1362812_2014_LW450Duo_TechSheet_v7.indd		
		SCHAWK JOB # : 310253C	CATEGORY OF WORK : COLLATERALS-FACT BOOKS	
		NRM JOB # : 1362812	NO. OF PAGES# : 3 PAGE	
	COMPONENT # : N/A	SIZE : A4		
NOTE :				