

Project..... Comments.....

Fixture Type..... Prepared By.....

Product Description:

High output LED lamp. Unique far infrared ceramic thermal management. Dimmable with most Uk and European dimmers. High colour rendering index (RA) 80. Average lifetime 40,000 hours. 3 years guarantee.

Product Image & Dimensions:



Overall Diameter	50 mm
Overall Length	58 mm
Overall Height	58 mm

Product Specifications:

- Lamp Type: GU10
- Lamp Base: GU10
- Input Voltage (Min): 220 V
- Input Voltage (Max): 240 V
- Input Voltage Type: AC
- Dimmable: Yes
- Beam Angle: 38 °
- Lifespan: 40000 hrs
- No. of LEDs: 3
- Overall Diameter: 50 mm
- Overall Length: 58 mm
- Overall Height: 58 mm
- Guarantee: 3 Years

Compliance & Approvals:



SKU Table and Ordering:

SKU Code	Wattage	Colour Temperature	Lumens	Candelas	EAN	Qty
AU-DGU106/30	6 W	3000 K	330 lm	570 cd	5055155484279	<input type="text"/>
AU-DGU106/40	6 W	4000 K	360 lm	620 cd	5055155484286	<input type="text"/>

Warranty:

For available warranty information for this product, please visit:

<http://gb.auroralighting.com/Products/Lamps/Firetec-LED-Lamps/240V-GU10/240V-GU10-6W-Dimmable-LED-Lamp.aspx>

UK Sales

16 Alban Park
Hatfield Road, St. Albans
United Kingdom
PH: +44 (0) 1727 83 66 11
FX: +44 (0) 1727 83 66 22

UK Distribution

Apex Park, 6 Little Burrows
Burrowfields, Welwyn Garden City
AL7 4SW
United Kingdom
PH: +44 (0) 1707 35 18 20
FX: +44 (0) 1727 35 18 21