

LED LENSER® L7 Polycarbonate Torch

Travelling light? This high-tech torch is perfect for expeditions and adventure travel but sits just as readily in a builder's toolbox. It is made from tough, weight-saving polycarbonate, which is temperature-resistant from -175 to +175 degrees, making it a willing companion everywhere from icy mountain tops to scorching dry deserts. It has an ultra-powerful high-end LED, which can light up to 225 metres and is enough to pick out the smallest detail in the most remote spots – perhaps across a valley, through the trees or down a ravine. An easy Twist Focus at one end spreads or concentrates light from close-ups to distance viewing and thanks to LED Lenser's patented Advanced Focus System the light quality remains constant and homogenous throughout: there are no dark rings or spots to confuse or break up the scene for the user. The L7 takes three AAA batteries. These are easy enough to get hold of practically anywhere but it is still nice to know that the burn time is up to 42 hours. It is also reassuring that the energy will be conducted as efficiently as possible through the gold-plated battery contacts inside the housing. Supplied with wrist strap and batteries.

As a leading international brand of hand-held torches and head lamps, LED Lenser is renowned for superior German engineering, outstanding performance, and state-of-the art technologies, such as the patented Advanced Focus System and Smart Light Technology. Constantly driving innovation to provide class-leading lighting instruments, LED Lenser is the brand of choice for professional tradesmen, emergency services personnel, search & rescue teams and serious outdoor enthusiasts. LED Lenser hand torches and head lamps deliver breath-taking, bright homogenous white light, that turns night into day and simply has to be seen to be believed. Using only the finest materials, such as energy-efficient CREE LED light chips, aircraft-grade aluminium and gold-plated contacts, they are renowned for quality and have a reputation for reliability that is second to none.

- The perfect tool-kit or expedition torch with a shockproof light-weight Polycarbonate housing and long run-time
- Polycarbonate is extremely resistant to both extreme cold or hot temperatures
- Energy efficient CREE Power LED Light Chip
- State-of-the-art, reliable German engineering
- Advanced Focus System™ Optics. Patented reflector and lens combination for intense spot (distance) or flawless flood (near) illumination - twist head to focus
- Tail cap on-off twist switch with integrated touch button ideal to signal manually (e.g. Morse)
- Corrosion resistant gold plated contacts for better conductivity
- Water and dust resistant. IPX54

Technical Information

Size: 133 x 37mm Ø

Power: 115 lumens max

Run Time: up to 42 hours

Beam Distance: up to 225m

Weight: 135grams

Supplied with : Wrist-strap and Duracell® batteries (3xAAA)

Code	Colour	Packaging	Barcode
7008	Black	Test-It Box	4029113700801