

Specifications for BMP51/53 Labelmaker Tape

Adhesive	Permanent Acrylic
Application	Control Panel & Electrical Panel Labels; Indoor & Outdoor Grade Facility & Safety Identification
Article No.	143390
Brady Material No.	B-595
Material Type	Vinyl
Colour	White on Blue
Finish	Gloss
Description	Durable, low-shrink vinyl with our most aggressive adhesive. Conforms to irregular, curved, rough and highly textured surfaces (painted cinder blocks, uneven wood, textured plastics, paper jacketed pipes, powder coated surfaces). Also adheres to difficult low energy surface items (PVC piping, blow-moulded equipment cases, ABS plastics, recycled plastics)
Max. Service Temp. °C	82
Order Reference	MC-1500-595-BL-WT
Printer Compatibility	BMP51; BMP53
Shape	Continuous
Size - Length (m)	7.62
Size - Width (mm)	38.10
Total Qty per Pack	1 Label(s) / Box
Industry	Electrical;Facility & Safety Identification;Process
Layout	Continuous Roll
Min. Application Temp. °C	-18
Min. Service Temp. °C	-40
Thickness (mm)	0.1