



ENGLISH

Datasheet

Blue 30m Nylon Air Hose, -40 → +80°C, Application Various

RS Stock number [415-0323](#)



Product Details

Light Duty Nylon Tube

Suitable for a wide range of light duty applications in compressed air, fuel and oil lines, breather pipe and greasing applications

Manufactured to BS5409 Part 1 and ISO7628 Part 1 & 2

30m coils

RS, Professionally Approved Products, gives you professional quality parts across all product categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.

Push-in System - Nylon Tube

All coils shown are non anti-static.

Specifications

[Find alternatives](#)

To find a similar product, based on selected attributes, click the green button

Application	Air Brake, Fuel & Lube Applications, Industrial & Automotive Production Lines, Instrumentation & Secondary Air Systems
Colour	Blue
Hose Inside Diameter	4.5mm
Hose Outside Diameter	6mm
Length	30m
Manufacturer Series	NLF
Material	Nylon
Maximum Operating Pressure	16 bar
Maximum Operating Temperature	+80°C
Minimum Operating Temperature	-40°C