

# Datasheet

## 2way Iso Passive AA converter 4-20mA

RS Stock number 794-8520



### Microcompact Passive Analogue/Analogue Converters

DIN rail mounting Microcompact passive analogue/anologue converters for industrial applications.

2-way isolation

Suppressor diode (33 V)

Screw terminals

IP 20 protection

Input Range	4 → 20 mA
Input Type	Analogue
Maximum Operating Temperature	+60°C
Minimum Operating Temperature	-25°C
Mounting Type	DIN Rail
Operating Temperature Range	-25 → +60 °C
Output Range	4 → 20 mA
Output Type	Analogue
Signal Conditioner Type	Isolation