



1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-8 GHz
- 1.2 NOMINAL IMPEDANCE: 75 OHM
- 1.3 VSWR: 1.3 MAX.

2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3604

3.0 FINISHES AND OTHERS

- 3.1 SEE BELOW TABLE FOR DETAILS.

4.0 ENVIRONMENTAL

- 4.1 OPERATING TEMPERATURE RANGE: -40° C TO +60° C

NO	DESCRIPTION	MATERIAL	Q'TY	FINISH
3	CENTER CONTACT	PHOSPHOR BRONZE	1	GOLD
2	INSULATION	PP	2	LIGHT BLUE
1	BODY	BRASS	1	NICKEL 100μ" MIN.



APPROVED by _____ DATE: _____

DESCRIPTION		F JACK - F JACK ADAPTER	
製圖	Yoko	TOLERANCE	品名
檢圖	Arc	.X ±0.2	18-20-13 PP.G.N
認定	Lewis	.XX ±0.1	ROHS COMPLIANT (750)
		.XXX ±0.05	DATE
		ANGLE ±5°	05.31.10'
			版次
			A-0
			UNIT
			mm(in)
			DWG.NO.
			18-0031
			SCALE
			4:1