


# 26 22 200


## Snipe Nose Side Cutting Pliers (Stork Beak Pliers)



- Elastic tips: dimensionally stable even when twisted
- Distortion-tolerant, elastic precision tips
- Half-round, long, tapered jaws
- With cutting edges (hardness approx. 61 HRC) for soft, medium-hard and hard wire
- Vanadium electric steel, forged, multi stage oil-hardened



<b>Article No.</b>	26 22 200
<b>EAN</b>	4003773010920
<b>Head</b>	polished
<b>Handles</b>	with multi-component grips
<b>Pliers</b>	black atramentized
<b>Style</b>	2
<b>Cutting capacities medium hard wire (diameter) Ø mm</b>	3,2
<b>Cutting capacities hard wire (diameter) Ø mm</b>	2,2
<b>T1 mm</b>	9,5
<b>W3 mm</b>	18
<b>W4 mm</b>	3,0
<b>T2 mm</b>	2,5
<b>L4 mm</b>	23,0
<b>L3 mm</b>	73,0
<b>Dimensions angle °</b>	40
<b>Length mm</b>	200
<b>Net weight g</b>	197



technical change and errors excepted

