

## PRECISION WIRE STRIPPERS

- Compact precision wire strippers for repeatable, damage free stripping of PVC, Teflon & similar coated wire
- Graduated depth stop for stripping to precise lengths
- Specially hardened blades for outstanding long term performance

- Fully ESD compliant for safe use on sensitive electronic components
- Adjustable to strip 6 wire diameters



### Wire stripper 3757ESD

BS EN 61340 2



| Item Number | Ø                                    |   |
|-------------|--------------------------------------|---|
| T3757ESD 2  | 0.25, 0.30, 0.40, 0.50, 0.60, 0.80mm | 1 |

- For fibre optic cable



### Wire stripper 3755

| Item Number | Ø      |   |
|-------------|--------|---|
| T3755 018   | 0.18mm | 1 |



### Wire stripper 3756

| Item Number | Ø      |   |
|-------------|--------|---|
| T3756 20    | 0.20mm | 1 |
| T3756 25    | 0.25mm | 1 |
| T3756 30    | 0.30mm | 1 |
| T3756 40    | 0.40mm | 1 |
| T3756 50    | 0.50mm | 1 |
| T3756 60    | 0.60mm | 1 |
| T3756 80    | 0.80mm | 1 |
| T3756 100   | 1.00mm | 1 |

- Adjustable to strip 6 wire diameters



### Wire stripper 3757

| Item Number | Ø             |   |
|-------------|---------------|---|
| 330009      | 0.12 - 0.40mm | 1 |
| 330013      | 0.25 - 0.80mm | 1 |
| 330011      | 0.30 - 1.00mm | 1 |

- Adjustable to strip 6 wire diameters



### Wire stripper 3759

| Item Number | Ø                                    |   |
|-------------|--------------------------------------|---|
| 330012      | 0.25, 0.30, 0.40, 0.50, 0.60, 0.80mm | 1 |



## CARBOFIB ESD DISSIPATIVE TWEEZERS

ABLEITFÄHIGE PINZETTEN  
BRUCELLES DISSIPATIVES  
PINZAS ANTIESTÁTICAS

### 1 Carbon fibre tips allow for safe handling of highly sensitive electrical components

Carbonfiberspitzen ermöglichen die sichere Handhabung von hochempfindlichen, elektrischen Komponenten  
Pointes en fibre de carbone pour la manipulation en toute sécurité des composants électriques hautement sensibles  
Puntas de fibra de carbono que permiten una manipulación segura de componentes muy sensibles

### 2 High grade, stainless steel bow – acid & corrosion resistant

Hochwertiger Edelstahlbügel - säure- und korrosionsresistent  
Branches en acier inoxydable- résistantes aux acides et à la corrosion  
Arco de acero inoxidable de alta calidad, resistente a la corrosión y al ácido

### 3 Precision welded joint for consistent, repetitive action

Präzise verschweißte Verbindungsstelle für stabile Handhabung und lange Lebensdauer  
Assemblage par soudage de précision pour une action répétitive constante  
Articulación soldada de precisión para que accione de manera coherente y repetitiva

### 4 Fully ESD compliant for safe use on sensitive electronic components

Vollständig ESD-konform, ableitfähig in allen Bereichen  
Entièrement conformes ESD pour une utilisation en toute sécurité sur les composants électroniques sensibles  
Cumple por completo la normativa eléctrica para ESD, para uso seguro con componentes electrónicos sensibles

### 5 Anti-magnetic to prevent electro-magnetic damage

Anti-magnetisch  
Antimagnétiques pour prévenir les dégâts électromagnétiques  
Amagnéticas para evitar los daños electromagnéticos

### 6 Heat resistant up to 270°C for safe use

Hitze resistent bis zu 270°C  
Réfractaires à la chaleur jusqu'à 270°C pour une utilisation en toute sécurité  
Resistente al calor, hasta los 270°C para un uso seguro

