

FatMax®



FatMax® Heavy Duty Fast-Travel Trigger Clamp

- ➔ Quickly converts from a clamp to a spreader without the use of tools
- ➔ Removable bar design integrates longer or shorter bars, as needed
- ➔ Dual Pivot Trigger offers fast closing and high clamping force
- ➔ Clamps in any position along the bar
- ➔ Removable jaw pads protect surfaces from marring and damage
- ➔ Reinforced nylon and steel construction provides strength and durability
- ➔ Clamping forces of up to 90kg

STANLEY	83-004	83-005	83-006
Weight in g	875	1030	1160
Throat Depth (mm)	88	88	88
Clamping Capacity (mm)	150	300	455
Clamping Capacity (inches)	6	12	18
Spreading capacity (mm)	390	540	695
Bar length (mm)	398	550	702
Clamping force (kg)	90	90	90

STANLEY	83-007	83-008
Weight in g	1300	1605
Throat Depth (mm)	88	88
Clamping Capacity (mm)	610	910
Clamping Capacity (inches)	24	36
Spreading capacity (mm)	850	1150
Bar length (mm)	855	1160
Clamping force (kg)	90	90