



Save as PDF



Peli protector cases - Crushproof peli case - 1120 case



Black Yellow Orange

Peli protector cases - Crushproof peli case - 1120 case SPECIFICATIONS

Exterior Dimensions (L x W x D)		Interior Dimensions (L x W x D)			
20.6 x 16.7 x 9 cm (8" x 7" x 4")		18.4 x 12.1 x 7.8 cm (7" x 5" x 3")			
Lid Depth		Bottom Depth		Total Depth	
1.3 cm (1")		6.5 cm (2.56")		7.8 cm (3.06")	
Lid Depth		Bottom Depth		Total Depth	
1.3 cm (0.50")		6.5 cm (2.56")		7.8 cm (3.06")	
Weight w/Foam		Weight w/o Foam		Buoyancy Max.	
0.56 kg. (1.23 lbs)		0.53kg (1.17 lbs.)		2.27 kg (5 lbs.)	
Range Temperature					
-40 / 99° C (-40 / 210° F)					

1120 Case Certificates

- IP67(1 meter submersion for 30 minutes)
- Def Stan 81-41/STANAG 4280

Interior dimensions:

18.4 x 12.1 x 7.8 cm (7" x 5" x 3")

Watertight, crushproof, and dust proof

Open cell core with solid wall design - strong, light weight

O-ring seal

Automatic Pressure Equalization Valve

Stainless steel hardware

Pick 'N' Pluck™ with convoluted lid foam

Unconditionally Guaranteed

Materials

Body	Latch	Lid O-Ring	Pins
Polypropylene	Polypropylene	PolymerStainless Steel	
Foam	Purge Body	Purge Vent	Purge O-Ring
1.3 lb Polyurethane	ABS	3 Micron Hydrophobic Non- Woven PET	70 Shore Nitrile

Configuration

Cat. #	Description
1120	Peli protector cases - Crushproof peli case - 1120 case

Peli protector cases - Crushproof peli case - 1120 case Accessories

Cat. #	Description