

HIGH POWER SOLDERING IRONS

S RANGE

- Wooden handle
- Nickel coated copper bit
- Large thermal capacity
- Thermally balanced
- Standard (ST), Angled (SR), & Hatchet (SH) versions available
- Heavy duty flexible rubber power cable



Hatchet (SH)

SPECIFICATIONS

Model	POWER	BIT SIZE	TEMP °C	LENGTH (mm)	WEIGHT (g)
ST20	200	19	430	340	850
ST25	250	19	460	340	850
ST32	325	22	510	340	1030
ST45	450	32	420	410	1615
ST50	500	32	470	410	1615
SR25A	250	19	450	324 (250)	900
SR32A	325	22	460	330 (260)	1030
SR45A	450	32	480	355 (270)	1615
SR50A	500	32	500	355 (270)	1615
SH25	250	19	450	324 (250)	900
SH32	325	22	460	330 (260)	1030
SH45	450	32	480	355 (270)	1615
SH50	500	32	500	355 (270)	1615

- Manufactured to Din EN 60335-2-45
- CE & EMC Low Voltage directive conformity



Angled (SR)

Standard (ST)