

EK EKPE 180 G



Sample photo

Order symbol: EKPE 180 G
Product nbr: 2538046
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074013590
El. number:
Finland: 3425422
Italy: 7501145
Sweden: 2538046

Including: Flanged Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		380	280	180	Ingress Protection (EN 60529): IP 66/67
inch:		15.0	11.0	7.1	Impact Resistance (EN 62262): IK 08
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate		Halogen free (DIN/VDE 0472, Part 815): Yes	
Base colour:		RAL 7035		UV resistance: UL 508	
Cover colour:		RAL 7035		Flammability Rating (UL 746 C 5): UL 746C 5V	
Cover screws material:		Polyamide		Glow Wire Test (IEC 695-2-1) °C: 960	
Cover screws colour:		Grey		NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12	
Gasket material:		Polyurethane			
Temperatures:					Certificates:
Short term:		-40 ... 120 °C		Germanischer Lloyd (GL)	
Continuous:		-40 ... 80 °C		Underwriters Laboratories	
Short term:		-40 ... 250 °F		Det Norske Veritas	
Continuous:		-40 ... 175 °F		Bureau Veritas	
Accessories:					Fimko
EKPE		Base, PC		Lloyds Register of Shipping (LR)	
EKPG		Base, PC		Europe EN 62208: 2003	
EKP 30-G		Cover		UL Canada	
EKP 80-G		Cover		Gost R	
EKP 30-T		Cover			
EKP 80-T		Cover			
EKPVT		Mounting plate			
EKPXT		Mounting plate Pertinax			
EKV 22		DIN-35 Mounting rail			
EKV 32		DIN-35 Mounting rail			
EKPZR		Extension frame			

