

Datasheet

RS Pro Straight 75Ω Coaxial Adapter Female 0 to 1GHz

RS Stock No: **546-4099**



Product Details

RS Pro straight female coaxial adapter has a nickel plated body, nuts and washers and a gold plated centre contact. It has 75 Ω impedance and operating frequency of 0 to 4 GHz. It is suitable for a variety of applications including video signalling and test equipment.

Features and Benefits

- Female coaxial adapter
- Nickel plated body, nuts and washers and a gold plated centre contact
- Suitable for a variety of applications including video signalling and test equipment

Specifications:

Adapter Type A	BNC
Adapter Type B	Coaxial
Adapter Type	BNC Socket to Coaxial Plug
Body Orientation	Straight
Body Plating	Nickel
Contact Material	Brass
Contact Plating	Gold
Gender A	Female
Gender B	Female
Impedance	75 Ω
Length	32.5 mm
Operating Frequency	0 to 1 GHz
Polarity	Normal
Body Material	Brass
Insulation Material	PTFE
Operating Temperature	-65 to +165°C
Voltage Rating	500 V