






ELV AND RoHS COMPLIANT




SECTION A-A



SECTION B-B

NOTES

- 適合ハウジング: 504186-****, 504193-****
APPLICABLE HOUSING : 504186-****, 504193-****
- アプリケーション仕様書 (コネクタ取扱説明書) : AS-504186-001/-002
AS-504193-001/-002
APPLICATION SPECIFICATIONS (CONNECTOR MANUAL) : AS-504186-001 / -002
AS-504193-001 / -002
- 圧着条件については、圧着仕様書 (CS-504185-002) を参照願います。
PLEASE REFER TO CRIMP SPECIFICATION (CS-504185-002).
- 製品仕様書: PS-504186-001 / PS-504193-001
PRODUCT SPECIFICATION : PS-504186-001 / PS-504193-001
- 圧着視覚教材 (品質要領書) : ATS-57427-0000
CRIMPING VISUAL AID : ATS-57427-0000



MATERIAL 材料	
銅合金, 錫めっき PRE-TINNED COPPER ALLOY	
WIRE RANGE 適用電線範囲	AWG : #26~#30 MM ² : 0.079~0.136
INS. RANGE 被覆外径	φ0.78~φ1.02

RELEASED EC NO: J2014-0152 DRWN:SSAT002 CHKD:KASAKAWA APPR:NUKITA	2013/07/25 2013/07/30 2013/08/08
--	--

GENERAL TOLERANCES (UNLESS SPECIFIED)	
10 UNDER	±0.2
10 OVER 30 UNDER	±0.25
30 OVER	±0.3
ANGULAR	±1 °
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

DIMENSION STYLE MM ONLY	
DRAWN BY	DATE
SSAT002	2013/07/25
CHECKED BY	DATE
KASAKAWA	2013/07/30
APPROVED BY	DATE
NUKITA	2013/08/08
MATERIAL NO.	
SEE TABLE	
SIZE	A3

SCALE 20:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION
1.25 W/B CONN. REC. CRIMP TERM.		
molex		
DOCUMENT NO. SD-504185-001		SHEET NO. 1 OF 1
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		