



全漢企業股份有限公司
FSP TECHNOLOGY INC.

台灣桃園市建國東路22號 統一編號：84239055
No. 22, Jianguo East Road., Taoyuan City, Taiwan, R.O.C.
TEL:+886-3-375-9888 Website : www.FSP-group.com
FAX:+886-3-375-6966 Email : sales@fsp-group.com.tw




MECHANICAL DRAWING



FSP300-60GHS(85),(F22001)

Released Date:2009/10/9-16:25:46

REF. ID/NO	PIN SIGNAL	WIRE COLOR	GAUGE	CONNECTOR TYPE	CABLE LENGTH
P1/24	1 +3.3VDC	ORANGE	18	WST P20-42002K11D+ P4-42002K11D or EQUIV.	380±28mm
	2 +3.3VDC	ORANGE	18		
	3 COM	BLACK	18		
	4 +5VDC	RED	18		
5	COM	BLACK	18		
6	+5VDC	RED	18		
7	COM	BLACK	18		
8	PW_OK	GRAY	24		
9	+5Vsb	PURPLE	20		
10	+12V1	YELLOW	18		
11	+12V1	YELLOW	18		
12	+3.3VDC	ORANGE	18		
13	+3.3VDC	ORANGE	18		
14	+3.3Vsb	BROWN	24		
15	-12VDC	BLUE	24		
16	PS_ON#	BLACK	18		
17	COM	GREEN	24		
18	COM	BLACK	18		
19	COM	BLACK	18		
20	COM	BLACK	18		
21	+5VDC	RED	18		
22	+5VDC	RED	18		
23	+5VDC	RED	18		
24	COM	BLACK	18		
P3	1 COM	BLACK	18	MOLEX 39-01-2040 or EQUIV.	500±28mm
	2 COM	BLACK	18		
	3 +12V2	YEL/BLK	18		
	4 +12V2	YEL/BLK	18		
P4	1 +3.3VDC	ORANGE	20	MOLEX SD-67582-001 or EQUIV.	250±28mm
	2 COM	BLACK	20		
	3 +5VDC	RED	20		
	4 COM	BLACK	20		
PB	1 +3.3VDC	ORANGE	20	MOLEX SD-67926-0011 or EQUIV.	450±28mm
	2 COM	BLACK	20		
	3 +5VDC	RED	20		
	4 COM	BLACK	20		
	5 +12V1	YELLOW	20		
P4	1 +12V1	YELLOW	20	AMP 1-480424-0 or EQUIV.	320±28mm
	2 COM	BLACK	20		
	3 COM	BLACK	20		
	4 +5VDC	RED	22		
P5	1 +12V1	YELLOW	22	AMP 1-480424-0 or EQUIV.	170±10mm
	2 COM	BLACK	22		
	3 COM	BLACK	22		
	4 +5VDC	RED	22		
P7	1 +5VDC	RED	24	AMP 171822-4 or EQUIV.	140±10mm
	2 COM	BLACK	24		
	3 COM	BLACK	24		
	4 +12V1	YELLOW	24		



P/N.:9PA300CW01

MODEL NO.:FSP300-60GHS(85).(F22001)

TITLE:ASSY

SHEET: 1 OF 1 REV:01

R&D 8

PE

DRAWN

DATE

XIAHOUYJ

2009-10-08

- NOTE:
1. ALL THE LENGTH OF OUTPUT WIRES EXCLUDE HOUSING.
 2. 產地標籤依業務指示加貼.

UNIT:mm



Mechanical Drawing(外觀/機構圖)表單編號:000P-0111