

# Tmax - Molded Case Circuit Breakers Cable Operated Flange Configurations

ABB Low Voltage Products and Systems is pleased to introduce the new line of cable operated flange handles, cables and mechanisms compatible with Tmax Molded Case Circuit Breakers (T1, T2, Ts3, T4, T5).

## New Flange Cable Operated Range

- Modern design
- 2 Handle types
  - NEMA 1, 3R, 12 - Gray painted
  - NEMA 4/4X - Nickel coated
- 7 Cable lengths
  - Mounting flexibility
  - 36" to 108" cables for molded case circuit breakers
- Merchandised component part structure, a complete assembly will require ordering:
  - 1 Tmax breaker (T1-T5), 1 mechanism, 1 handle, 1 cable, 1 lug kit (where applicable)



## Flange Handles – UL file # E116596

For use with	Environmental Rating	Catalog Number
T1, T2	NEMA 1, 3R, 12	OHF1C12T
	NEMA 4 & 4X	OHF1C4T
T3	Available Q4 2010	
Ts3, T4, T5	NEMA 1, 3R, 12	OHF1C12
	NEMA 4 & 4X	OHF1C4
T6*	NEMA 1, 3R, 12	K7FCH
	NEMA 4 & 4X	K7FCH4
T7, T8	Not Available	

\*Not UL listed

## Operating Mechanisms

For use with	Catalog Number
T1, T2	MKCT2
T3	Available Q4 2010
Ts3, T4	MKCT4
T5	MKCT5
T6*	K6FPM
T7, T8	Not Available

\*Not UL listed

## Flexible Cables

For use with	Cable Length (inches)	Catalog Number
T1, T2, Ts3, T4, T5	36	OXC1L36
	48	OXC1L48
	60	OXC1L60
	72	OXC1L72
	84	OXC1L84
	96	OXC1L96
	108	OXC1L108
T3	Available Q4 2010	
T6*	48	K7C048
	60	K7C060
	72	K7C072
	84	K7C084
	96	K7C096
120	K7C120	
T7, T8	Not Available	

\*Not UL listed

## Door Hardware

Item	Catalog Number
Safety door latch 2 point, door less than 40" high	KDH2R
Safety door latch 3 point, door less than 40" high	KDH3R

Power and productivity  
for a better world™

