

Product Information

ETX085x95-Ø20 NL100-Type A

EAN 4031582330946

Wheel centre made of steel, tread made of Polyurethane, casted, precision ball bearing, sealed

Wheel diameter	85 mm
Width of Tread	95 mm
Axle Hole Ø	20 mm
Hub length	100 mm
Temperature	- 20 / + 60 °C
Dynamic Load capacity	1000 kg
Static Load capacity	2000 kg
Hardness of tread	A 92 Shore

