

LED-25-8V/12V/24V DC

SPECIFICATIONS

Standards

Converter meets CE standard
UL class 2 recognized component
File # E164062

Available Versions

901025008-LED 25 8V DC
901025012-LED 25 12V DC
901025024-LED 25 24V DC

Mechanical and Thermal

Dimensions 30mm x 43mm x 157mm
Weight 140 grams
Tc Max 90°C
Ta Max 50°C
PC plastic casing
Terminal Block Connection

**Electrical**

Load	1-25VA
Input	90-277V 50/60Hz
Output at Max. load	8V/12V/24VDC
Power Factor	0.96
Efficiency	86%
THD max	8%
EMC (RFI)	FCC Class B/EN 55015
Harmonics	EN 61000
Immunity	EN 61547/61047
SELV	

Protection and Regulation

Electronic internal resettable short circuit protection.
Overload and thermal regulation.
Voltage Regulation.

