

**LIGHTS**  
**3610**  
 Little Ed™ Zone 0

Save as PDF



**Peli lights - Zone 1 Torch - LED technology lights**

The body is made of tough ABS resin that's corrosion proof and resistant to extreme temperatures. It is powered by 4 AA alkaline cells. Certified to ATEX Zone 0 (Category 1).



**Peli lights - Zone 1 Torch - LED technology lights**  
**ANSI FL1 Specifications**

**Materials**

Body	Lens	Shroud	Switch Type
EXL	Polycarbonate Resin	ABS	One-handed safety switch

	High	
<b>LIGHT SOURCE.</b>	LED	
<b>BATTERIES</b>	4 AA Alkaline (Not included)	
<b>CHARGE TIME</b>	N/A	
<b>VOLTAGE</b>	6	
<b>LENGTH</b>	19.1 cm (7.51")	
<b>WEIGHT W/ BATTERIES</b>	0.17 kg (6 oz.)	
<b>WEIGHT W/O BATTERIES</b>	0.2 kg (6.9 oz.)	






**LIGHT OUTPUT**

**RUNTIME (hours/min)**


**BEAM DISTANCE (meters)**

**PEAK BEAM INTENSITY (candela)**

**WATER RESISTANT**

<b>FL1 STANDARD</b>	High	
		
	7h 30m	
	161m	
	6500cd	
		

### Approvals

CE  - II 1 G Ex ia IIC T4 Ga, II 1 D Ex ia IIIC T135??C  
 Da IP66  
 Certificate: ITS09ATEX26183X

	RESIST	Safety switch operation	
<b>Clip</b>	<b>Contact, Spring &amp; Retainer</b>	<b>O-Ring</b>	<b>Night Vision Film</b>
Stainless Steel	Stainless Steel; Phosphore Bronze and Brass Nickel Plate	Ethylene Propylene	N/A

### Configuration

Cat. #	Description
--------	-------------

### Peli lights - Zone 1 Torch - LED technology lights Accessories

No accessories are currently available for this product