

# Ordering information

## Accessories

OXP12X\_  
S00047A



### Shafts

The type and ordering numbers are for one piece

Shaft length [mm]	H [mm]	Suitable for switches	Type	Order number	Delivery batch [pcs]	Weight/unit [kg]
<b>Shaft diameter 12 mm</b>						
166	146...226	OT315...400	OXP12X166	1SCA022325R7100	1	0.20
185	165...245	OT315...400	OXP12X185	1SCA022325R6710	1	0.20
250	230...310	OT315...400	OXP12X250	1SCA022325R6980	1	0.28
280	260...340	OT315...400	OXP12X280	1SCA022137R5140	1	0.30
325	305...385	OT315...400	OXP12X325	1SCA022042R5810	1	0.36
395	375...455	OT315...400	OXP12X395	1SCA022042R5990	1	0.43
465	445...525	OT315...400	OXP12X465	1SCA022042R6020	1	0.51
535	515...595	OT315...400	OXP12X535	1SCA022042R6110	1	0.59
250	230...345	OT630...800	OXP12X250	1SCA022325R6980	1	0.28
280	260...375	OT630...800	OXP12X280	1SCA022137R5140	1	0.30
325	305...420	OT630...800	OXP12X325	1SCA022042R5810	1	0.36
395	375...490	OT630...800	OXP12X395	1SCA022042R5990	1	0.43
465	445...560	OT630...800	OXP12X465	1SCA022042R6020	1	0.51
535	515...630	OT630...800	OXP12X535	1SCA022042R6110	1	0.59
250	221...350	OT1000...2500	OXP12X250	1SCA022325R6980	1	0.28
280	251...380	OT1000...2500 <sup>1)</sup>	OXP12X280	1SCA022137R5140	1	0.30
325	296...425	OT1000...2500 <sup>1)</sup>	OXP12X325	1SCA022042R5810	1	0.36
395	366...495	OT1000...2500 <sup>1)</sup>	OXP12X395	1SCA022042R5990	1	0.43
465	436...565	OT1000...2500 <sup>1)</sup>	OXP12X465	1SCA022042R6020	1	0.51
535	506...635	OT1000...2500 <sup>1)</sup>	OXP12X535	1SCA022042R6110	1	0.59
325	340...535	OETL3150	OXP12X325	1SCA022042R5810	1	0.36
395	410...605	OETL3150	OXP12X395	1SCA022042R5990	1	0.43
465	480...675	OETL3150	OXP12X465	1SCA022042R6020	1	0.51
535	550...745	OETL3150	OXP12X535	1SCA022042R6110	1	0.59

<sup>1)</sup> Wide versions OT1000-2500W.; with shafts over 280 mm, shaft tube OXT20X210X must be used, see page 53