

General Information

Extended Product Type:	PC8-4
Product ID:	1SNA116540R2500
EAN:	3472591165401
Catalog Description:	PC8-4 Lateral Jumper Bars Black
Long Description:	PC8-4 - Lateral Jumper Bars - 4 poles - Black - 8mm Spacing

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Lateral Jumper Bars

Ordering

EAN:	3472591165401
Minimum Order Quantity:	10 piece
Customs Tariff Number:	39269097

Dimensions

Product Net Weight:	6 g
---------------------	-----

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Gross Weight:	0.06 kg
Package Level 1 EAN:	3472591165401
Package Level 2 Units:	1500 piece

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
--------------------------	--

Technical UL/CSA

Flammability According to UL94:	V0
---------------------------------	----

Additional Information

Ambient Temperature:	-5 ... +40 °C
Color:	Black
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Function:	Lateral Jumper Bars
IIT Publishing Status:	Level 0 - Information enabled
Insulation Material:	Polyamide
Mounting Type:	1 - Rated voltage: 630 V (IEC) / 150 V (UL) (I) 2 - Rated voltage: 630 V (IEC) / 300 V (UL) (II) a - End section ES10-ST (II) b - End stop BAZ1
Product Main Type:	PC
Product Name:	Jumper Bar
Rated Current (I _n):	Main Circuit 50 A
Rated Voltage (U _r):	630 V
Spacing:	8 mm
Sub-Function 2:	Lateral
Suitable For:	D6/8.ADO DB4/8.A.ADO3 DB4/8.ADO DH4/8.A.ADO DH4/8.ADO DR4/8.A.ADO3 DRE4/8.A.ADO3 DS4/8.A.ADO3 DS4/8.ADO DSE4/8.A.ADO3 DSE4/8.ADO E6/8 ES8-CG M6/8.SNB M6/8.ST M6/8.STP MS6/8 ZS10-PE-R1 ZS10-R1 ZS10-ST ZS10-ST-1

Certificates and Declarations (Document Number)**Data Sheet, Technical Information:** 1SNK160027C0205**Declaration of Conformity - CE:** 1SND225001C1009**Classifications****ETIM 4.0:** EC000489 - Cross-connector for terminal block**ETIM 5.0:** EC000489 - Cross-connector for terminal block**Object Classification Code:** X