

# Datasheet

## FLUSH-MOUNTING SOCKET 6P+E IP44 32A 6h






| TechData                   |                       |
|----------------------------|-----------------------|
| Rated current              | 32A                   |
| Commercial series          | OPTIMA-SEVEN Series   |
| Poles                      | 6P+E                  |
| Hour position              | 6h                    |
| Rated voltage              | 380-415V              |
| Working frequency          | 50Hz                  |
| Working frequency          | 60Hz                  |
| Colour                     | RED                   |
| Syntetical description     | FLUSH-MOUNTING SOCKET |
| Protection degree          | IP44                  |
| Types of available outlets | STRAIGHT              |

### Approvals and Certifications

**CE** CE Declaration of conformity

### Standards and Laws

-  EN 60309-1 (1999) [European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements
-  EN 60309-1/A1 (2007) [European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements
-  EN 60309-1/A2 (2012) [European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements

### Packaging

| Description  | Box              |
|--------------|------------------|
| Quantity     | 10               |
| Gross weight | 2.68 KG          |
| Volume       | 8436 CCM         |
| Dimensions   | 185x285x160 (MM) |