


## Crimp contact - CK1,6-ED-0,37BU AG - 1663394

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Turned 1.6 crimp contact, individual female contact, core diameter 0.14 to 0.37 mm<sup>2</sup>, silver-plated



### Key commercial data

Packing unit	100 pc
GTIN	 4 017918 123208
Weight per Piece (excluding packing)	0.72 g
Custom tariff number	85366990
Country of origin	Germany

### Technical data

#### Electrical characteristics

Note	For HC-M-12, HC-M-EMC, HC-D, HC-DD and VC-D contact inserts, the quality of a crimp connection is determined by DIN EN 60 352-2
------	---

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

#### Mechanical characteristics

Conductor cross section	0.14 mm <sup>2</sup> ... 0.37 mm <sup>2</sup>
Connection cross section AWG	26 ... 22
Stripping length of the individual wire	8 mm (6 mm in case of 2.5 mm <sup>2</sup> )
Insertion/withdrawal cycles	≥ 500

#### General

Type	Individual female contact
Series	HC-M-12
Connection method	Crimp connection
Assembly instructions	At voltages of < 5 V and currents < 5 mA, gold-plated contacts are recommended.

# Crimp contact - CK1,6-ED-0,37BU AG - 1663394

## Technical data

### General

Connection	For HC-M-12..., HC-M-03/04..., HC-M-17..., HC-M-EMV..., HC-D..., HC-DD..., VC-D.. contact carriers
------------	--

### Material data

Contact material	Copper alloy
Contact surface material	Silver-plated

## Classifications

### eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

### ETIM

ETIM 2.0	EC000796
ETIM 3.0	EC000796
ETIM 4.0	EC000796
ETIM 5.0	EC000796

### UNSPSC

UNSPSC 6.01	30211923
UNSPSC 7.0901	39121522
UNSPSC 11	39121522
UNSPSC 12.01	39121522
UNSPSC 13.2	39121522

## Approvals

### Approvals

---

#### Approvals

UL Recognized / GOST

---

#### Ex Approvals

---

## Crimp contact - CK1,6-ED-0,37BU AG - 1663394

### Approvals

Approvals submitted

---

#### Approval details

UL Recognized 

GOST 

### Accessories

#### Accessories

#### Assembly tool

Assembly tool - CK1,6/2,5-MWZ - 1676734



Assembly tool, for CK 1.6... crimp contacts for small conductor cross sections

---

Contact removal tool - VC-EW 1,6 - 1884869



Contact removal tool, for turned and rolled CK- 1.6-... contacts

---

#### Crimping tool

Crimping pliers - CRIMPFOX-1,6/2,5-ED-4,0 - 1687419




Crimping pliers, for turned contacts, CK 1.6 ED... and CK 2.5 ED...

---

### Drawings

## Crimp contact - CK1,6-ED-0,37BU AG - 1663394

Dimensioned drawing



Dimensional drawing