




A-A
SCALE 2:1



B-B
SCALE 2:1



REMARK:

1. MATERIALS:

CONTACTS: COPPER ALLOY T=0.20mm, GOLD(G\F or 30u") TOP OVER CONTACT AREA, 50u" Min. NICKEL UNDER PLATE.

2. PART NUMBER DESCRIPTION: 10090933-S XX X X LF

SERIES NO. TYPE S: SOCKET (FEMALE) GAUGE SIZE 24: 24-28(AWG) CONTACT FINISH 4: GOLD FLASH 6: 30u" GOLD LF: ROHS COMPLIANT PACKAGING 8: BOX, 500 PCS 9: REEL, 10K PCS

SIZE	PART NO.	PACKAGING
24-28AWG	10090933-S24*8LF	BOX, 500PCS
24-28AWG	10090933-S24*9LF	REEL, 10KPCS

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	FCI www.fciconnect.com
ltr	ecn no	dr	date	linear	angles		
A	T09-1157	J.H	12/10/09	.X ± 0.38	0° ± 2°	projection	title
B	T10-0164	J.H	10/19/10	.XX ± 0.25		MM	H/D D-SUB CRIMPING FEMALE CONTACT
				.XXX ± 0.10		scale	product family D-SUB
						1:1	size dwg no
							A4 10090933
							code TWN
							sheet 1 of 1
sheet index	revision sheet	B	1				

cage code