



ENGLISH

Datasheet

Stock No: 291-3611

# RS Pro Brass Cable Gland Kit, 6.4 → 7.9mm Cable Dia., 3 Cores



## Product Details

### Cable Seals for 20mm Glands

Operating temp -20°C to +105°C

Pack contains all the items to make a termination

10 seals per bag

## Specifications:

Material	Brass
Minimum Cable Diameter	6.4mm
Maximum Cable Diameter	7.9mm
Kit Includes	Brass Locknuts, Complete Straight Through Joint, Conductor Insulating Sleeving, Earth Tail Seal Kit, Insulated Glands, One Hole Clip Reference Bare, Plain Seal Kit, Shroud, Two Way Saddle Reference Bare, Zinc Plated Steel Lockwasher
Number of Cores	3
Minimum Operating Temperature	-20°C
Maximum Operating Temperature	+105°C