

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
HM	00		E	REV; ECO-14-004548	26MAR2014	GG	JG

- 1

DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
- 2


MATERIAL: HOUSING- POLYCARBONATE, CLEAR
TERMINAL - .36 [.014] THICK PHOSPHOR BRONZE PLATED WITH .178 μ m[.000007] THICK GOLD IN LOCALIZED PLATE AREA, OVER .762 μ m[.000030] THICK PALLADIUM NICKEL IN LOCALIZED PLATE AREA OVER 2.54 μ m[.000100] THICK NICKEL ON ENTIRE CONTACT.
3.

PLUG WILL ACCEPT 24 TO 28 AWG STRANDED WIRE, 0.74-0.99 [.029-.039] DIAMETER, WITH A 5.34 [.210] DIAMETER JACKET.
- 4

TERMINATED DIMENSION 6.15 [.242] MAXIMUM.
- 5

500 ASSEMBLIES PER PACKAGE.
- 6

100 ASSEMBLIES PER PACKAGE.



6	5-557963-3
5	5-557963-2
PACKAGED	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. SIMPSON 24-APR-93	TE TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK C. WHITT 11-MAY-93				
		APVD M. HAWKINS 14-MAY-93	NAME			
		PRODUCT SPEC 108-1163	MODULAR PLUG ASSEMBLY, 10 POSITION, ROUND CABLE, STRANDED WIRE			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 114-6016	SIZE A2	CAGE CODE 00779	DRAWING NO C=557963	RESTRICTED TO -
MATERIAL		WEIGHT -	CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 1
					REV E	