



Datasheet

ENGLISH

Stock No: 285-7814

RS Pro Green, Unscreened Single Core Equipment Wire, 0.25 mm² CSA , 500 V 6 A, 100m



Product Details

Flexivolt®

Flexivolt® is polyvinylchloride, especially designed for electro-technical application, for example internal wiring onto moving parts with average mechanical use, installation and equipment and car construction. This PVC compound shows good mechanical properties. It is completely flexible at temperatures from -10°C to +60°C and suitable for continuous use.

CSA (mm ²)	Conductor Strands (mm)	AWG	Cable O/D (mm)	Insulation Thickness (mm)	Current Rating (A)	Voltage Rating (V)
0.1	26 / 0.07	27	1.0	0.3	2	150
0.15	39 / 0.07	26	1.5	0.5	4	500
0.25	65 / 0.07	23	1.7	0.5	6	500
0.5	129 / 0.07	20	2.1	0.5	10	500



ENGLISH

Specifications:

Cross Sectional Area	0.25 mm ²
Sheath Colour	Green
Core Strands	65/0.07 mm
Insulation Material	PVC
Outer Diameter	1.7mm
Length	100m
Number of Strands	65
Current Rating	6 A
Voltage Rating	500 V
Size of Strands	0.07 mm
Minimum Operating Temperature	-10°C
Maximum Operating Temperature	+60°C
Cable Shape	Single Core
Insulation Wall Thickness	0.5mm
Type	Unscreened