





LOC		DIST		REVISONS			
F	LYR	DESCRIPTION		DATE	DWN	APVD	
	B2	REVISED PER ECO-10-006160		27APR2010	DCS	DCS	



- 1 ACCEPTS #4 SELF TAPPING THREAD CUTTING SCREWS OR METRIC EQUIVALENT. DRIVE TO 0.6 N-m MAX
- 2 DATE CODE IN THIS LOCATION USING 5 DIGIT CODE
FIRST 2 DIGITS = YEAR, SECOND 2 DIGITS = WEEK
LAST DIGIT = DAY.
- 3 MATERIALS: HEADER HOUSING - GLASS FILLED PBT
PINS - TIN OR GOLD PLATED BRASS
- 4 HOUSING COLORS ARE MECHANICALLY KEYED TO MATE ONLY WITH IDENTICALLY COLORED PLUG ASSEMBLIES.
- 5. HEADER MATES TO PLUG ASSEMBLY 776286 WHICH USES REELED TERMINAL 770520 OR LOOSE PIECE TERMINAL 770854.




RECOMMENDED P.C. BOARD LAYOUT
FOR 1.57 THICK P.C. BOARD




776275-2 & 1-776275-2
KEY LOCATION
SCALE 2:1

776275-1 & 1-776275-1 SHOWN


NATURAL	DURAGOLD	1-776275-2
BLACK	DURAGOLD	1-776275-1
NATURAL	TIN	776275-2
BLACK	TIN	776275-1
HEADER COLOR 4		PLATING
		PART NUMBER



RECOMMENDED MOUNTING HOLE LAYOUT
FOR 5.0 MAX THICK PANEL



SECTION A-A
OPTIONAL CONSTRUCTION IF PANEL
THICKNESS IS GREATER THAN 2.0



SECTION A-A
OPTIONAL CONSTRUCTION IF PANEL
THICKNESS IS GREATER THAN 2.0

TYP. IS FOR REFERENCE TO CHANGES TO THIS DRAWING FOR YOUR ELECTRONIC CORPORATION. IF IT IS FOR PUBLICATION, IT SHALL BE CONTACTED FOR THE LATEST REVISION.		DWN D. STRAUSSER 29 JAN 2010	Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS:		CHK D. STRAUSSER 22 MAR 2010	NAME	
mm		APVD D. STRAUSSER 27 APR 2010	ASSEMBLY, HEADER, 8 POSITION, VERTICAL, AMPSEAL	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	SIZE	
0 PLC ±.1		108-1329	CAGE CODE	
1 PLC ±0.2		APPLICATION SPEC	DRAWING NO	
2 PLC ±0.13		114-16016	A100779C=776275	
3 PLC ±.1		WEIGHT	RESTRICTED TO	
4 PLC ±.1		-	SCALE	
ANGLES		CUSTOMER DRAWING	4:1	
FINISH			SHEET	
3			1 OF 1	
			REV	
			B2	