



ENGLISH

RS Pro 300mm Long EPDM 15 bar Braided Stainless Steel Hose

RS Stock No. 711-8448

Brand RS Pro



Product Details

Braided Flexible Tap Connectors - DM Push Fit

Braided AISI 304 stainless steel flexible tap connectors with swivel female nut and DM plastic (acetal) push fit fitting. For DM push fit with isolation valve, see [711-8436](#). For DM to DM, see [711-8445](#).

5 year Service Life

Suitable for hot and cold potable water

Non toxic EPDM lining that does not promote microbiological growth

DM fittings made from acetal (Kepital F10-03H)

Approvals

WRAS & BS6920



Hose Assemblies

Specifications

Not what you're looking for? Select the attributes you require, then click the button below

<input type="checkbox"/>	Length	300mm
<input type="checkbox"/>	Connection 1	15 mm Push Fit
<input type="checkbox"/>	Connection 2	1/2 in BSP Female
<input type="checkbox"/>	Liner Material	EPDM
<input type="checkbox"/>	Suitable Applications	Cold Water, Hot Water
<input type="checkbox"/>	Maximum Working Pressure	15 bar
<input type="checkbox"/>	Connection Material 1	Stainless Steel
<input type="checkbox"/>	Connection Material 2	Plastic
<input type="checkbox"/>	Connection Size 1	1/2in
<input type="checkbox"/>	Connection Size 2	15mm
