

All Purpose Cable Lockout with Non-Conductive Nylon Cable (2.44 m)



Lock out multiple control points with a single device. Perfect for your unusual energy isolating devices that are difficult to lock out. Easy to use - simply hold device in one hand and clinch tight with the other! Supplied with nylon cable

Overview

Specifications

Article Number: 050941

Order Reference: 050941

Description: All Purpose Cable Lockout with Non-Conductive Nylon Cable (2.44 m)

Colour: Red

Material Type: Impact-Resistant Nylon

Risk: Mechanical Risk

QTY/UOM: 1/pk

Min. Shackle Clearance (mm): 20

Max. Shackle Diameter (mm): 7

Cable Length (m): 2.44