

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [120119-0006](#)
Status: **Active**
Overview: Brad® Ultra-Lock® Connection System
Description: Ultra-Lock® Molded Junction Box, Top Mount Mini-Change® (M23) Home Run Connector, 4 Port, Mini-Change 19 Pole Dual I/O, PNP

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Passive Distribution Boxes
Series	120119
IP Rating	IP68
NEMA Rating	NEMA 6
Overview	Brad® Ultra-Lock® Connection System
Product Name	Ultra-Lock® (M12)
UPC	78678884411

Physical

Bus I/O	Ultra-Lock® (M12)
Cable Connector Orientation	N/A
Cable Length	N/A
Home Run Cable Length	N/A
Home Run Connector	M23 - 19 pole
Home Run Interface	Integrated Connector
Keyway	Single
LED Indicator	Yes
Material - Cable Jacket	N/A
Material - Housing	PBT
Material - Metal	Copper Alloy
Material - Plating Mating	Gold over Nickel
Net Weight	999.990/kg
Orientation	Top Mount
Poles	5
Poles (wired)	5
Ports	4
Temperature Range - Operating	-25°C to +90°C
Wiring Configuration	Dual I/O per Port

Electrical

Current - Maximum per Contact	12A per module, 4A per port
Functional Wiring	PNP
Voltage - Maximum	10-30V DC

Material Info

Old Part Number	BKY403P-FBC
-----------------	-------------

Reference - Drawing Numbers

Sales Drawing	SD-120119-011
---------------	---------------



image - Reference only

Series

EU RoHS

RoHS Compliant by Exemption
REACH SVHC Not Reviewed
Low-Halogen Status Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[120119Series](#)