

Interface module - DFLK 50 - 2280284


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



The VARIOFACE feed-through module implements a 1:1 connection between screw connection terminal blocks and an IDC/FLK pin strip (2.54 mm, number of positions: 50).



Key commercial data

Packing unit	5 pc
GTIN	 4 017918 054397
Weight per Piece (excluding packing)	155.4 g
Custom tariff number	85369010
Country of origin	Germany

Technical data

Dimensions

Width	39 mm
Height	143.4 mm
Depth	49 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Nominal voltage U_N	< 50 V AC 60 V DC
Max. current carrying capacity per branch	1 A
Max. total current of all branches	50 A ($T_A = 50^\circ\text{C}$)
Number of positions	50
Status display	No
Mounting position	any
Standards/specifications	Air and creepage distances DIN EN 50178 basic insulation
Pollution degree	2

Interface module - DFLK 50 - 2280284

Technical data

General

Surge voltage category	II
Rated surge voltage	0.6 kV
Rated insulation voltage	63 V

Connection data for connection 1

Connection name	Field level
Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Stripping length	8 mm
Screw thread	M3

Connection data for connection 2

Connection name	Control system level
Number of connections	1
Connection method	IDC/FLK pin strip (2.54 mm)
Number of positions	50

Classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152

ETIM

ETIM 2.0	EC001434
ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC002780

UNSPSC

UNSPSC 6.01	30211824
-------------	----------

Interface module - DFLK 50 - 2280284

Classifications

UNSPSC

UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

Approvals

Approvals


Approvals

GOST

Ex Approvals

Approvals submitted

Approval details



Accessories

Accessories

System cable

Cable - FLK 50/EZ-DR/ 50/KONFEK - 2289065



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 0.5 m

Cable - FLK 50/EZ-DR/ 100/KONFEK - 2289078



Round cable sets, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 1 m

Interface module - DFLK 50 - 2280284

Accessories

Cable - FLK 50/EZ-DR/ 150/KONFEK - 2289081



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 1.5 m

Cable - FLK 50/EZ-DR/ 200/KONFEK - 2289094



Round cable sets, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 2 m

Cable - FLK 50/EZ-DR/ 250/KONFEK - 2289104



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 2.5 m

Cable - FLK 50/EZ-DR/ 300/KONFEK - 2289117



Round cable sets, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 3 m

Cable - FLK 50/EZ-DR/ 350/KONFEK - 2289120



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 3.5 m

Interface module - DFLK 50 - 2280284

Accessories

Cable - FLK 50/EZ-DR/ 400/KONFEK - 2289133



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 4 m

Cable - FLK 50/EZ-DR/ 450/KONFEK - 2289573



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 4,5 m

Cable - FLK 50/EZ-DR/ 500/KONFEK - 2289586



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 5 m

Cable - FLK 50/EZ-DR/ 550/KONFEK - 2289599



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 5,5 m

Cable - FLK 50/EZ-DR/ 600/KONFEK - 2289609



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 6 m

Interface module - DFLK 50 - 2280284

Accessories

Cable - FLK 50/EZ-DR/ 650/KONFEK - 2289612



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 6.5 m

Cable - FLK 50/EZ-DR/ 700/KONFEK - 2289625



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 7 m

Cable - FLK 50/EZ-DR/ 750/KONFEK - 2289638



Round cable set, with two 50-pos. female connectors (1:1 connection), for connecting 32 channels, cable length: 7.5 m

Cable - FLK 50/EZ-DR/ 800/KONFEK - 2289641



Round cable sets, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 8 m

Cable - FLK 50/EZ-DR/ 850/KONFEK - 2289654



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 8.5 m

Interface module - DFLK 50 - 2280284

Accessories

Cable - FLK 50/EZ-DR/ 900/KONFEK - 2289667



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 9 m

Cable - FLK 50/EZ-DR/ 950/KONFEK - 2289670



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 9.5 m

Cable - FLK 50/EZ-DR/1000/KONFEK - 2289683



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 10 m

Cable - FLK EZ-DR.../.../... - 2295059



Round cable, with preassembly, not shielded, variable cable length

Cable - FLK 50/EZ-DR/ 50/KONFEK/S - 2299097



Round shielded cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 0.5 m

Interface module - DFLK 50 - 2280284

Accessories

Cable - FLK 50/EZ-DR/ 100/KONFEK/S - 2299107



Round shielded cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 1 m

Cable - FLK 50/EZ-DR/ 150/KONFEK/S - 2299110



Round shielded cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 1.5 m

Cable - FLK 50/EZ-DR/ 200/KONFEK/S - 2299123



Round shielded cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 2 m

Cable - FLK 50/EZ-DR/ 300/KONFEK/S - 2299136



Round shielded cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 3 m

Cable - FLK 50/EZ-DR/ 400/KONFEK/S - 2299149



Round shielded cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 4 m

Interface module - DFLK 50 - 2280284

Accessories

Cable - FLK 50/EZ-DR/ 600/KONFEK/S - 2299152



Round shielded cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 6 m

Cable - FLK 50/EZ-DR/ 800/KONFEK/S - 2299165



Round shielded cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 8 m

Cable - FLK 50/EZ-DR/1000/KONFEK/S - 2299178



Round shielded cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 10 m

Cable - FLK EZ-DR-S.../.../... - 2295046




Round cable, with preassembly, shielded, variable cable length


Drawings

Interface module - DFLK 50 - 2280284

Dimensioned drawing



Dimensioned drawing



Interface module - DFLK 50 - 2280284

