


Hazardous substances label - PML-GHS100 (13X13)R - 1014289

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Hazardous substances label, Roll, red/white, Pre-printed, can be labeled with: THERMOMARK ROLL, THERMOMARK X, Mounting type: Adhesive, Lettering field: 13 x 13 mm

Why buy this product

- Stick-on hazardous substances labels, color preprinted, without symbol
- The markers conform to the GHS international standard
- High temperature resistance
- High adhesive strength
- Suitable for indoor and outdoor use



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 787048
Weight per Piece (excluding packing)	110.5 g
Custom tariff number	39199000
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length (b)	13 mm
Width (a)	13 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
---------------------------------	-------------------

General

Color	red/white
Type	Diamond
Components	Silicone-free
Material	Polyester

Hazardous substances label - PML-GHS100 (13X13)R - 1014289

Technical data

General

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	500
Number of individual labels per row	3
Marking mounting type	Adhesive

Classifications

eCl@ss

eCl@ss 4.0	27141199
eCl@ss 4.1	27141199
eCl@ss 5.0	27371301
eCl@ss 5.1	27371301
eCl@ss 6.0	27371301
eCl@ss 7.0	27371301
eCl@ss 8.0	27141137

ETIM

ETIM 3.0	EC000712
ETIM 4.0	EC002498
ETIM 5.0	EC001777

UNSPSC

UNSPSC 6.01	43172501
UNSPSC 7.0901	43212107
UNSPSC 11	43172501
UNSPSC 12.01	43212107
UNSPSC 13.2	43212107

Accessories

Accessories

Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon, Length: 300000 mm, Width: 110 mm, Color: black

Labeled systems marker

Hazardous substances label - PML-GHS100 (13X13)R - 1014289

Accessories

Pipeline markers - PML-T101 (26X280)R CUS - 1014249

Pipeline markers, can be ordered: By line, green, labeled according to customer specifications: Water, Mounting type: Adhesive, Lettering field: 26 x 280 mm



Pipeline markers - PML-T101 (52X560)R CUS - 1014250

Pipeline markers, can be ordered: By line, green, labeled according to customer specifications: Water, Mounting type: Adhesive, Lettering field: 52 x 560 mm



Pipeline markers - PML-T102 (26X280)R CUS - 1014251

Pipeline markers, can be ordered: By line, red, labeled according to customer specifications: Steam, Mounting type: Adhesive, Lettering field: 26 x 280 mm



Pipeline markers - PML-T102 (52X560)R CUS - 1014252

Pipeline markers, can be ordered: By line, red, labeled according to customer specifications: Steam, Mounting type: Adhesive, Lettering field: 52 x 560 mm



Pipeline markers - PML-T103 (26X280)R CUS - 1014253

Pipeline markers, can be ordered: By line, gray, labeled according to customer specifications: Air, Mounting type: Adhesive, Lettering field: 26 x 280 mm



Hazardous substances label - PML-GHS100 (13X13)R - 1014289

Accessories

Pipeline markers - PML-T103 (52X560)R CUS - 1014254

Pipeline markers, can be ordered: By line, gray, labeled according to customer specifications: Air, Mounting type: Adhesive, Lettering field: 52 x 560 mm



Pipeline markers - PML-T104 (26X280)R CUS - 1014255

Pipeline markers, can be ordered: By line, yellow/red, labeled according to customer specifications: Flammable gases, Mounting type: Adhesive, Lettering field: 26 x 280 mm



Pipeline markers - PML-T104 (52X560)R CUS - 1014256

Pipeline markers, can be ordered: By line, yellow/red, labeled according to customer specifications: Flammable gases, Mounting type: Adhesive, Lettering field: 52 x 560 mm



Pipeline markers - PML-T105 (26X280)R CUS - 1014257

Pipeline markers, can be ordered: By line, yellow/black, labeled according to customer specifications: Non-flammable liquids, Mounting type: Adhesive, Lettering field: 26 x 280 mm



Pipeline markers - PML-T105 (52X560)R CUS - 1014258

Pipeline markers, can be ordered: By line, yellow/black, labeled according to customer specifications: Non-flammable liquids, Mounting type: Adhesive, Lettering field: 52 x 560 mm



Hazardous substances label - PML-GHS100 (13X13)R - 1014289

Accessories

Pipeline markers - PML-T106 (26X280)R CUS - 1014259

Pipeline markers, can be ordered: By line, orange, labeled according to customer specifications: Acids, Mounting type: Adhesive, Lettering field: 26 x 280 mm



Pipeline markers - PML-T106 (52X560)R CUS - 1014260

Pipeline markers, can be ordered: By line, orange, labeled according to customer specifications: Acids, Mounting type: Adhesive, Lettering field: 52 x 560 mm



Pipeline markers - PML-T107 (26X280)R CUS - 1014261

Pipeline markers, can be ordered: By line, violet, labeled according to customer specifications: Alkalis, Mounting type: Adhesive, Lettering field: 26 x 280 mm



Pipeline markers - PML-T107 (52X560)R CUS - 1014262

Pipeline markers, can be ordered: By line, violet, labeled according to customer specifications: Alkalis, Mounting type: Adhesive, Lettering field: 52 x 560 mm



Pipeline markers - PML-T108 (26X280)R CUS - 1014263

Pipeline markers, can be ordered: By line, brown/red, labeled according to customer specifications: Flammable liquids, Mounting type: Adhesive, Lettering field: 26 x 280 mm



Hazardous substances label - PML-GHS100 (13X13)R - 1014289

Accessories

Pipeline markers - PML-T108 (52X560)R CUS - 1014264

Pipeline markers, can be ordered: By line, brown/red, labeled according to customer specifications: Flammable liquids, Mounting type: Adhesive, Lettering field: 52 x 560 mm



Pipeline markers - PML-T109 (26X280)R CUS - 1014265

Pipeline markers, can be ordered: By line, brown/black, labeled according to customer specifications: Non-flammable liquids, Mounting type: Adhesive, Lettering field: 26 x 280 mm



Pipeline markers - PML-T109 (52X560)R CUS - 1014266

Pipeline markers, can be ordered: By line, brown/black, labeled according to customer specifications: Non-flammable liquids, Mounting type: Adhesive, Lettering field: 52 x 560 mm



Pipeline markers - PML-T110 (26X280)R CUS - 1014267

Pipeline markers, can be ordered: By line, blue, labeled according to customer specifications: Oxygen, Mounting type: Adhesive, Lettering field: 26 x 280 mm



Pipeline markers - PML-T110 (52X560)R CUS - 1014268

Pipeline markers, can be ordered: By line, blue, labeled according to customer specifications: Oxygen, Mounting type: Adhesive, Lettering field: 52 x 560 mm



System marking

Hazardous substances label - PML-GHS100 (13X13)R - 1014289

Accessories

Pipeline markers - PML-T101 (26X280)R - 1014229

Pipeline markers, Roll, green, Pre-printed, can be labeled with: THERMOMARK ROLL, THERMOMARK X, Mounting type: Adhesive, Lettering field: 26 x 280 mm



Pipeline markers - PML-T101 (52X560)R - 1014230

Pipeline markers, Roll, green, Pre-printed, can be labeled with: THERMOMARK ROLL, THERMOMARK X, Mounting type: Adhesive, Lettering field: 52 x 560 mm



Pipeline markers - PML-T102 (26X280)R - 1014231

Pipeline markers, Roll, red, Pre-printed, can be labeled with: THERMOMARK ROLL, THERMOMARK X, Mounting type: Adhesive, Lettering field: 26 x 280 mm



Pipeline markers - PML-T102 (52X560)R - 1014232

Pipeline markers, Roll, red, Pre-printed, can be labeled with: THERMOMARK ROLL, THERMOMARK X, Mounting type: Adhesive, Lettering field: 52 x 560 mm



Pipeline markers - PML-T103 (26X280)R - 1014233

Pipeline markers, Roll, gray, Pre-printed, can be labeled with: THERMOMARK ROLL, THERMOMARK X, Mounting type: Adhesive, Lettering field: 26 x 280 mm



Hazardous substances label - PML-GHS100 (13X13)R - 1014289

Accessories

Pipeline markers - PML-T103 (52X560)R - 1014234

Pipeline markers, Roll, gray, Pre-printed, can be labeled with: THERMOMARK ROLL, THERMOMARK X, Mounting type: Adhesive, Lettering field: 52 x 560 mm



Pipeline markers - PML-T104 (26X280)R - 1014235

Pipeline markers, Roll, yellow/red, Pre-printed, can be labeled with: THERMOMARK ROLL, THERMOMARK X, Mounting type: Adhesive, Lettering field: 26 x 280 mm



Pipeline markers - PML-T104 (52X560)R - 1014236

Pipeline markers, Roll, yellow/red, Pre-printed, can be labeled with: THERMOMARK ROLL, THERMOMARK X, Mounting type: Adhesive, Lettering field: 52 x 560 mm



Pipeline markers - PML-T105 (26X280)R - 1014237

Pipeline markers, Roll, yellow/black, Pre-printed, can be labeled with: THERMOMARK ROLL, THERMOMARK X, Mounting type: Adhesive, Lettering field: 26 x 280 mm



Pipeline markers - PML-T105 (52X560)R - 1014238

Pipeline markers, Roll, yellow/black, Pre-printed, can be labeled with: THERMOMARK ROLL, THERMOMARK X, Mounting type: Adhesive, Lettering field: 52 x 560 mm



Hazardous substances label - PML-GHS100 (13X13)R - 1014289

Accessories

Pipeline markers - PML-T106 (26X280)R - 1014239

Pipeline markers, Roll, orange, Pre-printed, can be labeled with: THERMOMARK ROLL, THERMOMARK X, Mounting type: Adhesive, Lettering field: 26 x 280 mm



Pipeline markers - PML-T106 (52X560)R - 1014240

Pipeline markers, Roll, orange, Pre-printed, can be labeled with: THERMOMARK ROLL, THERMOMARK X, Mounting type: Adhesive, Lettering field: 52 x 560 mm



Pipeline markers - PML-T107 (26X280)R - 1014241

Pipeline markers, Roll, violet, Pre-printed, can be labeled with: THERMOMARK ROLL, THERMOMARK X, Mounting type: Adhesive, Lettering field: 26 x 280 mm



Pipeline markers - PML-T107 (52X560)R - 1014242

Pipeline markers, Roll, violet, Pre-printed, can be labeled with: THERMOMARK ROLL, THERMOMARK X, Mounting type: Adhesive, Lettering field: 52 x 560 mm



Pipeline markers - PML-T108 (26X280)R - 1014243

Pipeline markers, Roll, brown/red, Pre-printed, can be labeled with: THERMOMARK ROLL, THERMOMARK X, Mounting type: Adhesive, Lettering field: 26 x 280 mm



Hazardous substances label - PML-GHS100 (13X13)R - 1014289

Accessories

Pipeline markers - PML-T108 (52X560)R - 1014244

Pipeline markers, Roll, brown/red, Pre-printed, can be labeled with: THERMOMARK ROLL, THERMOMARK X, Mounting type: Adhesive, Lettering field: 52 x 560 mm



Pipeline markers - PML-T109 (26X280)R - 1014245

Pipeline markers, Roll, brown/black, Pre-printed, can be labeled with: THERMOMARK ROLL, THERMOMARK X, Mounting type: Adhesive, Lettering field: 26 x 280 mm



Pipeline markers - PML-T109 (52X560)R - 1014246

Pipeline markers, Roll, brown/black, Pre-printed, can be labeled with: THERMOMARK ROLL, THERMOMARK X, Mounting type: Adhesive, Lettering field: 52 x 560 mm



Pipeline markers - PML-T110 (26X280)R - 1014247

Pipeline markers, Roll, blue, Pre-printed, can be labeled with: THERMOMARK ROLL, THERMOMARK X, Mounting type: Adhesive, Lettering field: 26 x 280 mm



Pipeline markers - PML-T110 (52X560)R - 1014248

Pipeline markers, Roll, blue, Pre-printed, can be labeled with: THERMOMARK ROLL, THERMOMARK X, Mounting type: Adhesive, Lettering field: 52 x 560 mm

