


7810 WITH THREADED FITTING, BSP PARALLEL AND METRIC



	C	E (mm)	E1 (mm)	F (mm)	H (mm)	J (mm)	L (mm)	 (kg)
7810 10 10	G1/8	5,0	8,0	13,0	38,0	15,0	17,0	0,040
7810 13 13	G1/4	8,0	12,0	17,0	40,0	18,0	24,0	0,000
7810 17 17	G3/8	7,0	12,0	20,0	53,0	22,0	24,0	0,000
7810 19 19	M5x0,8	4,0	4,0	8,0	24,0	10,0	11,0	0,028
7810 21 21	G1/2	8,0	15,0	23,0	69,0	28,0	31,0	0,020