

Datasheet

RS PSU-A395-010 Bench Power Supply, 1 Output 27V dc 2A

RS Stock 537-5371



Specification:

	MODEL A390	MODEL A395
Input Voltage	230V	
Input Frequency	50/60 Hz \pm 10%	
Output Voltage	13.5V at 4A d.c.	27.0V at 2A d.c.
Output Voltage Adjustment	11.5V to 14V d.c.	22V to 28V d.c.
Line Regulation	\pm 0.1%	
Load Regulation	\pm 0.1%	
Ripple and Noise	10Mv Vp-p	20Mv Vp-p
Dimensions	100 mm x 130 mm x 270 mm	
Weight	4.0 Kg	