

Handheld Labelling machine



With the PT-90 you will finally discover the fun way of keeping everything organised - anywhere in the home! This stylish labelling machine combines both fun and function, and is really simple to use. The large display gives a clear preview of the label before you print.

Key Features

- Save time with up to 7.5mm per second
- 9 & 12mm wide labels available
- Convenient built-in cutter
- Easy to use QWERTY keyboard
- Easy-to-read 12 character LCD screen
- Includes 12mm black on white tape (4m)

Supplies

| 9mm | 12mm |
|--------------------|---------|
| Non-laminated - 4m | |
| M-K221S | M-K231S |
| Non-laminated - 8m | |
| M-K221 | M-K231 |
| M-K222 | M-K232 |
| M-K223 | M-K233 |
| M-K521 | M-K531 |
| M-K621 | M-K631 |

Optional Extras

- AD24ES AC adapter

Product Specifications

| | |
|-------------------------------|---|
| Housing Colour | White |
| Key Board | QWERTY |
| Number of Keys | 45 |
| Cutter | Yes (Manual) |
| Power | AAA x 4pcs or Optional AC adapter |
| LCD | 12 chrs x 1 line / 50mm x 25mm |
| Print Method | Thermal |
| Print Head | 203dpi/ 64d ots |
| Print Speed | 7.5 mm / sec |
| Tape Type | M |
| Tape Width | Max. Label width 12mm |
| Max. Print Width | 7mm |
| Number of characters | 382 |
| Number of Symbols | 173 |
| Character Sizes | 6 (3 widths x 2 Heights) |
| Fonts | 1 (Helsinki) |
| Font Styles | 8 kinds (Normal, Bold, Outline, Shadow, Italic, Italic Bold, Italic Outline, Italic Shadow) |
| Frames | 7 kinds (Round, Leaf, Tile, Star, Heart, Bubble, Flower) |
| Underline | Yes |
| Strikeout | No |
| Multi-Line | 2 Lines |
| Multi-Block | No |
| Horizontal Alignment | Left (Centre, when you set the label length) |
| Vertical Alignment | No |
| Cable Labelling | No |
| Tape Length Setting | Yes (30-300mm) |
| Tape Margin Setting | Full (Narrow, when you set the label length) |
| Pre made Designs | 8 kinds |
| Memory | 240 chrs (3 areas x 80 chrs) |
| Barcodes | No |
| Time and Date function | No |
| Numbering | No |
| Mirror Printing | No |
| Vertical Printing | Yes (in style settings) |
| Repeat printing | Yes (1-9) |
| Print Preview | Yes (Text and label length) |
| Unit | Yes (inch/mm) |
| Language Change | 10 kinds (English, German, French, Spanish, Portuguese, Italian, Dutch, Danish, Norwegian, Swedish) |

Weights/ Dimensions/ Measures

Dimensions

156mm x 111mm x 57mm

Weight

250g

What's in the box

12mm Black on White tape (4M)

Users Guide

Warranty Card

