

LS LED

LS LED 900 15.3W 3000K

0050991



Range features

- Ultra slim cross section
- Silver housing and end-caps
- Integrated switch
- Structured diffuser for even light distribution
- 120° light beam
- LED technology: energy and maintenance savings of up to 75%
- Connect up to 10 fixtures in a row with direct connectors or flexible leads for wider spacing or corner connections
- Main cable with EURO-plug, direct and flexible connectors included
- Stainless steel mounting clips for easy installation included
- Available in 830 Homelight
- IP20 & CLASS II
- Mounting support for 90° tilt mounting supplied



PRODUCT OVERVIEW

| | |
|------------------------|-----------------|
| Ordering number | 0050991 |
| Technology | LED |
| EAN code | 5410288509914 |
| Mount | Ceiling surface |
| Colour temperature (K) | 3000 |
| Voltage (V) | 220-240 |
| Colour | Silver mat |
| Included lamp | Integrated LED |
| IP rating | 20 |
| IK rating | 2 |

LS LED

LS LED 900 15.3W 3000K

0050991

DATA TABLE

General data

| | |
|----------------------------------|---|
| Technology | LED |
| Ordering number | 0050991 |
| EAN code | 5410288509914 |
| E-number SE | 7010481 |
| E-number FI | 4273598 |
| Mount | Ceiling surface |
| Long description | Ultra slim cross section. Silver housing and end-caps. Integrated switch. Structured diffuser for even light distribution. 120° light beam. LED technology: energy and maintenance savings of up to 75%. Connect up to 10 fixtures in a row with direct connectors or flexible leads for wider spacing or corner connections. Main cable with EURO-plug, direct and flexible connectors included. Stainless steel mounting clips for easy installation included. Available in 830 Homelight. IP20 & CLASS II. Mounting support for 90° tilt mounting supplied |
| Product name | LS LED 900 15.3W 3000K |
| Control gear availability | Included |
| Control gear mounting | Integral |
| Control gear type | Electronic |
| Environment | Interior |
| Specific application | Ambient Illumination, Ceiling Voids, Kitchen, Shelves, Shoplighting, Under Cabinet, Workbenches |
| Sales pack quantity | 1 |

Optical data

| | |
|-------------------------------|-----------|
| Colour temperature (K) | 3000 |
| Distribution type | Symmetric |

Electrical data

| | |
|------------------------------------|---------|
| Total power consumption (W) | 15.3 |
| Voltage (V) | 220-240 |
| Glow wire test | 650°C |
| Leading trailing edge | No |
| Number of heads | 1 |
| Total number of lamps | 1 |

LS LED

LS LED 900 15.3W 3000K

0050991

Physical data


| | |
|---|----------------------|
| Maximum distance from luminaire (cm) | 100 |
| Weight (kg) | 0.53 |
| Colour | Silver mat |
| Lamp included | Yes |
| Included lamp | Integrated LED |
| Height (mm) | 36 |
| Width (mm) | 30 |
| Length (mm) | 916 |
| IP rating | 20 |
| IK rating | 2 |
| Diffuser finish | Mat, Ribbed |
| Single package dimensions (L x W x H) (cm) | 116.00 x 4.30 x 3.50 |
| Outer package dimensions (L x W x H) (cm) | 116.00 x 4.30 x 3.50 |

LS LED

LS LED 900 15.3W 3000K

0050991

TECHNICAL DRAWINGS



ENERGY LABEL

