



## Main

|                             |   |
|-----------------------------|---|
| Range                       | Spacial   |
| Product name                | Spacial SM  |
| Product or component type   | Compact enclosure   |
| Device application          | Multi-purpose   |
| Installation accessory type | Floor-standing  |
| Device composition          | 1 blocking system for left door<br>1 body<br>1 cable gland plate<br>1 mounting plate<br>1 locking system with handle for door<br>4 mounting plate bracket<br>2 door |
| Removable parts             | Door fixed by screws for hinge<br>Mounting plate bracket fixed by screws<br>Mounting plate fixed by screws for mounting plate bracket                               |
| Enclosure nominal height    | 2000 mm   |
| Enclosure nominal width     | 1200 mm   |
| Enclosure nominal depth     | 400 mm  |

## Complementary

|                             |  |
|-----------------------------|--|
| Number of doors             | 2 on front   |
| Door opening                | Left 120 °<br>Right 120 °  |
| Door type                   | Plain  |
| Lock type                   | 4 points lock, handle with 5 mm double bar insert  |
| Body type                   | Single piece body with welded rear panel<br>Front part forming a rigid frame with welded corners       |
| Mounting plate description  | Plain  |
| Type of gland plate         | Standard   |
| Cable entry                 | 1 entry  |
| Material                    | Galvanised steel for mounting plate<br>Sheet steel for body<br>Sheet steel for door<br>Zamak for hinge |
| Surface finish              | Epoxy-polyester powder   |
| Colour                      | Enclosure : grey RAL 7035<br>Handle : black RAL 9005   |
| Accessibility for operation | Front  |

## Environment

|                         |                              |
|-------------------------|------------------------------|
| standards               | IEC 62208                    |
| product certifications  | BV<br>DNV<br>UL              |
| IP degree of protection | IP55 conforming to IEC 60529 |
| IK degree of protection | IK10 conforming to IEC 62262 |

## Offer Sustainability

|                          |                       |
|--------------------------|-----------------------|
| Sustainable offer status | Green Premium product |
|--------------------------|-----------------------|

|                                  |   |
|----------------------------------|---|
| RoHS (date code: YYWW)           | Compliant - since 0940 - Schneider Electric declaration of conformity |
| REACH                            | Reference not containing SVHC above the threshold                     |
| Product environmental profile    | Available   |
| Product end of life instructions | Need no specific recycling operations                                 |

### Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|