


KEMET Part Number: LDEDC3100KA5N00
(DEDC3100KA5N00)

Capacitor, film, 0.1 uF, +/-10% Tol, General Purpose, 63VDC@125° C



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	4.7	+0.3/-0.2
W	3.3	+/-0.3
T	2.4	MAX

Packaging Specifications	
Package Kind:	T&R
Package Size:	330mm
Package Quantity:	3000

General Information	
Supplier:	KEMET

Specifications	
Capacitance:	0.1 uF
Dielectric:	Metallized PEN (Stacked)
Rated Temperature:	125° C
Voltage @ rated temp:	63VDC
Voltage AC:	40VAC
Tolerance:	+/-10%
Body Type:	Surface Mount
Chip Size:	1812
Application:	General Purpose
Temperature Range:	-55/+125C
Dissipation Factor @ 1 kHz:	0.8%
Insulation Resistance:	1 GOhm
Maximum dVdT:	100v/us