



QueueWay Retractable Posts

The QueueWay Retractable Post is an economy crowd control barrier, which features 2.3m webbing, an effective braking system and a locking tape end to avoid accidental release.

Features

- ➔ 2.3m of Black, Blue, Red, Yellow/Black Chevron Webbing
- ➔ Post and base available in two colours - Black or Mirror Effect
- ➔ Heavy gauge steel post won't dent and scratch like aluminium
- ➔ Locking tape end avoids accidental release
- ➔ Effective built-in braking system for slow, safe webbing retraction
- ➔ Full weight 356mm diameter base for maximum stability
- ➔ Full circumference rubber floor protector for maximum protection against floor scuffing
- ➔ Posts sold and shipped in pairs
- ➔ Posts distributed flat packed and are assembled within seconds without the use of tools
- ➔ Not compatible with Tensabarrier® posts
- ➔ Accommodates Tensator's range of sign holders
- ➔ Suitable only for indoor use

Benefits

- ➔ Discreetly guide & inform your customers & employees
- ➔ Easily achieve the optimum queue layout for your floor space
- ➔ Reduces customer stress by removing ambiguity as to where the customer should queue and by providing separation between individuals and queue lines

Safety Benefits

All crowd control products contain a powerful constant force spring, used to retract the belt. If the retraction mechanism is not fitted with a braking system, and the belt is accidentally released, the belt will snap back with enough force to cause injury.

QueueWay retractable webbing posts are fitted with a slow retract braking system as standard.

When making your purchasing decision ensure you give this complete consideration as there are cheaper alternatives that do not include this safety feature as standard.



Order Codes:

QWYPOST	QueueWay Retractable Posts
height	1016mm / 40"
base dia.	356mm / 12.5"
weight	9.5kg / 21 lbs

