

Position Measurement Sensor
F78S, F78C, F78B, F78E

Standard Precision MKV Potentiometers



Our line of Standard Precision MKV Potentiometers offer a cost effective way of obtaining high accuracy, long life position feedback. New England Instrument has many years of experience in successfully providing high reliability/high performance products to the military and aerospace industries and continues to expand that technical capability to the low cost/high performance industrial and commercial markets.

APPLICATIONS

Value Positioning
Panel Controls
Instrumentation
Missile Controls

INDUSTRY

Aerospace
Military
Commercial
Industrial



invensys

Sensor Systems

Position Measurement Sensor F78S, F78C, F78B, F78E

Standard Precision MKV Potentiometers

SPECIFICATIONS

MECHANICAL

Mechanical Travel:	360°
Mounting Type:	Bushing, Servo
Bearing Type:	Sleeve, Ball
Mounting Thread:	3/8-32NEF, 1/4-32NEF
Stop Strength (nominal):	n/a
Weight (max):	16 grams
Life Expectancy (cycles):	10mm - sleeve, 30mm - ball bearing
Torque (oz-in max):	0.5 - ball, 1.0 - sleeve
End Play (max):	0.005
Shaft Diameter (inches):	1/8 or 1/4

ELECTRICAL

Independent	
Linearity-Standard:	±1.0%, ±0.5%, ±0.25%*
Total Resistance (ohms) (Including Specials):	500 to 200k
Resistance	
Tolerance-Standard:	±10%
Theoretical Electrical Travel:	340°
Power Rating @ 70°C (watts):	1.0
Output Smoothness per MIL-R-39023:	0.5%, 0.25%, 0.15%
End Voltage (max) (% of total applied voltage):	1.0%
Dielectric Withstanding Voltage (RMS):	750
Insulation Resistance (min):	1000 megohms
Resolution (virtually infinite):	yes

ENVIRONMENTAL


Shock:	per MIL-STD-202
Vibration:	per MIL-STD-202
Temperature Range (operational):	-65°C to +125°C
Temperature Range (storage):	-65°C to +125°C

Unless Otherwise Specified

Decimal Dimensions:	±0.005
Fractional Dimensions:	±1/64

* Consult Factory for custom OEM configurations.

DIMENSIONS



ORDERING INFORMATION

F78S, F78C, F78B, F78E

F78S - A 103

Shaft Diameter
Blank-1/8" MKV
B1-1/4" MKV
except F78E

Standard Resistances

500	=	501
1,000	=	102
2,000	=	202
5,000	=	502
10,000	=	103
20,000	=	203
50,000	=	503
100,000	=	104

Linearity:

A	=	±1.0%
B	=	±0.5%
C	=	±0.25%

Type Number

F78S = Servo w/Ball bearing
F78C = Servo w/Sleeve bearing
F78B = Bushing 3/8-32 w/Sleeve bearing
F78E = Bushing 1/4-32 w/Sleeve bearing



invensys

Sensor Systems

1 401 769 0703
FAX: 401 769 0037

New England Instrument
245 Railroad Street
Woonsocket, RI 01895

www.speed-position.invensys.com

GENERAL DISCLAIMER: Invensys Sensor Systems reserves the right to make changes to its products and their specifications at any time, without prior notice to anyone. Invensys Sensor Systems has made every effort to ensure accuracy of the information contained herein but can assume no responsibility for inadvertent errors, omissions, or subsequent changes. Invensys Sensor Systems does not assume responsibility for the use of any circuit or other information described within this document, and further, makes no representations of any that the circuit and information described herein is free infringement of any intellectual property right or any other right of third parties. No express or implied licenses of any Invensys Sensor System intellectual property right is granted by implication or otherwise.